







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1560096	2015/05/11	Ruru	Change Logo



Section A-A



Note:
* Waterproof Rate: IP68
* Clamp Ring: Nylon, Gray
* Sealing Nut: Nylon, Gray
* Gasket: EPDM, Black
* Seals: EPDM, Black
* Cable Range: $\varnothing 10.0 \sim \varnothing 14.0 \text{mm}$
* Spanner Size:
Body: 27.2mm
Screw Nut: 29.0mm

UNIT:mm		 	TITLE Cable Gland for PG16,Gray (Short)			
TOLERANCE .X .XX .XXX ANGLES		± 0.25 ± 0.1 ± 0.05 $\pm 1^{\circ}$	SCALE 1:1	SIZE A4	SHEET 1	OF 1
			REV. B	WC-REV. A.1	QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO CSG-16G007	DRAWN BY Ruru	DATE 2015-05-11
DWG NO CSG-16G007	CHECKED BY Rita	DATE 2015-05-11
CUSTOMER ALTW	APPROVED BY Lion	DATE 2015-05-11

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CSG-16G007](#)