


## NOTES

- 1 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 2 - CORROSION RESISTANT STEEL ENCLOSURE, PLUNGER & ROLLER
- 3 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 3
- 4 - BASIC SWITCHES HAVE SOLID GOLD CONTACT MATERIAL
- 5 - SWITCH CURRENT LEVELS SHALL NOT BE MORE THAN 100 MILLIAMPS AT 28 VDC
- ⑥ PRINT CIRCUIT DIAGRAM, CATALOG LISTING, DATE CODE AND 1534AS392-1 ON NAMEPLATE
- ⑦ PLASTIC MATERIAL(S) SHALL CONFORM TO MIL-M-14 OR MIL-M-24519
- ⑧ 10X MIL-W-22759/11-22-9 WIRE LEAD MARKED WITH CIRCUIT IDENTIFICATION PER MIL-W-5088

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



SCALE 2:1

DO NOT SCALE PRINT

LESS OTHERWISE SPECIFIED  
TOLERANCES ARE

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		± 4°

WEIGHT

CHARACTERISTICS	ELECTRICAL DATA		
OPERATING FORCE - - - - - 3 ± 1 LBS	CONTACT ARRANGEMENT		
FULL OVERTRAVEL FORCE - - - - 7 LBS MAX	3X SPDT		
RELEASE FORCE - - - - - .5 LBS MIN	LOAD (AMPS)	28 VDC	
PRETRAVEL - - - - - .040 MAX		SEA LEVEL	50,000 FT
DIFFERENTIAL TRAVEL - - - - .020 MAX	RESISTIVE	1	1
OVERTRAVEL - - - - - .125 MIN	INDUCTIVE	.5	.5
	MOTOR	—	—

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[ML-1282](#)