


REV	DOCUMENT	CHANGED BY	CHECK
7	0011669	DVM 05MAR05	AK



NOTES:

- 1 - UNIT INCLUDES 2 EACH "23SX39-H58" TYPE (GOLD BASIC SWITCH CONTACTS)
- 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 3 - PLATED TERMINALS WILL ACCEPT "AMP INC." Ø.058 PIN RECEPTACLES
- 4 - DULL FINISH ON LEVER AND BUSHING
- 5 - SWITCH NUMBERS STAMPED ON END OF BASIC SWITCHES
- 6 - WHEN LEVER IS MOVED OUT OF A MAINTAINED POSITION, IT WILL RETURN OF ITS OWN ACCORD TO THE ORIGINAL POSITION OR THE ADJACENT POSITION. THE TOGGLE LEVER MAY HANG UP BETWEEN THE TWO ADJACENT POSITIONS ONLY BY EXERTING CONSIDERABLE EFFORT
- 7 - TERMINAL DESIGNATION STAMPED ON BOTH SIDES OF UNIT
- 8 - BUSHING SEALED TO PREVENT ENTRANCE OF LIQUID OR DUST
- 9 - POSITION NO. 1
- 10 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET 15PA313-AT PER MIL-PRF-8805
- 11 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA313-AT
- 12 - FOR MANUFACTURING DETAILS SEE THE CORRESPONDING ASSEMBLY DRAWING FOR EACH LISTING FOR FAA-PMA

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES X ± THIRD ANGLE PROJECTION 	DRAWN	TSM	04SEP01	<div>Honeywell</div>					
	CHECK	SAV	04SEP01						
	.030 .015 .005	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE ASSEMBLY - TOGGLE SWITCH				
		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY							
	Pro/ENGINEER 2D			SIZE B	TYPE I	DRAWING NAME 62AT39 SERIES CHART 1			REV 7
SCALE 1:1			WEIGHT .05LB EST		SHEET 1 OF 1				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[62AT39-3](#)