

REV	DOCUMENT	CHANGED BY	CHECK
14	0038162	BS 24MAR08	ASD

SERIES

DESIGNATES PRESSURE

L - LOW PRESSURE (IN H<sub>2</sub>O)  
- NO DESIGNATION (PSI)

PRESSURE RANGE

04, 10 IN H<sub>2</sub>O  
0.3, 01, 05, 15, 30,  
60, 100, 150 PSI

CPC

G

ACCURACY GRADE

C - COMMERCIAL GRADE  
H - HIGH GRADE

PORT OPTION

F - AXIAL  
- NO PORT/O-RING SEAL


PRESSURE REFERENCE

G - GAGE

CATALOG LISTINGS	
CPCL04GC	CPC15GFC
CPCL04GFC	CPC15GFH
CPCL10GFC	⑨
CPCL10GFH	CPC30GFC
CPCL10GH	CPC30GFH
⑪	CPC60GFH
CPC0.3GFC	⑨
CPC0.3GFH	CPC60GFC
CPC01GFC	CPC100GFH
CPC01GFH	CPC100GC
CPC01GH	CPC100GFC
CPC05GC	CPC150GFC
CPC05GFC	CPC150GFH
CPC05GFH	SCDA121 CPCL04GFC
CPC05GH	

G - STYLE (GAGE)	PERFORMANCE AT 25°C AND 12±0.01 V <sub>dc</sub> (UNLESS OTHERWISE STATED)									
	C-GRADE			H-GRADE			UNITS	FULL SCALE PRESSURE PSI	OVER PRESSURE PSI	
	MIN	NOM	MAX	MIN	NOM	MAX				
NULL OFFSET (0 PSIG) (L04 LISTING)	-2	0	2	N/A	N/A	N/A	mV			
NULL OFFSET (0 PSIG), ALL LISTINGS EXCEPT L04	-1	0	1	-0.5	0	0.5	mV			
4 IN H <sub>2</sub> O (P1>P2) (L04 LISTING)	23	25	27	N/A	N/A	N/A	mV <sub>dc</sub>	4 IN H <sub>2</sub> O	3	
4 IN H <sub>2</sub> O (P1>P2) (SCDA121 CPCL04GFC)	23	25	27	N/A	N/A	N/A	mV <sub>dc</sub>	4 IN H <sub>2</sub> O	5	
10 IN H <sub>2</sub> O (P1>P2) (L10 LISTING)	19	20	21	19.5	20	20.5	mV <sub>dc</sub>	10 IN H <sub>2</sub> O	5	
0.3 PSI SPAN (P1>P2)	19	20	21	19.5	20	20.5	mV <sub>dc</sub>	0.3	5	
1 PSI SPAN (P1>P2)	17	18	19	17.5	18	18.5	mV <sub>dc</sub>	1	5	
5 PSI SPAN (P1>P2)	57	60	63	59	60	61	mV <sub>dc</sub>	5	15	
15 PSI SPAN (P1>P2)	85	90	95	89	90	91	mV <sub>dc</sub>	15	45	
30 PSI SPAN (P1>P2)	85	90	95	89	90	91	mV <sub>dc</sub>	30	90	
60 PSI SPAN (P1>P2)	85	90	95	89	90	91	mV <sub>dc</sub>	60	180	
100 PSI SPAN (P1>P2)	95	100	105	99	100	101	mV <sub>dc</sub>	100	250	
150 PSI SPAN (P1>P2)	85	90	95	89	90	91	mV <sub>dc</sub>	150	250	
NULL SHIFT OVER TEMPERATURE (0-25, 25-70 °C)	---	---	±1	---	---	±.5	mV			
SPAN SHIFT OVER TEMPERATURE (0-25, 25-70 °C)	---	---	±2	---	---	±1	% SPAN			
COMBINED LINEARITY AND HYSTERESIS	---	0.25	1	---	0.25	0.5	% SPAN			

GENERAL OPERATING CHARACTERISTICS	ALL PRESSURES AND GRADES			UNITS
	MIN	NOM	MAX	
EXCITATION VOLTAGE	3	12	16	V <sub>dc</sub>
SUPPLY CURRENT	---	---	3.5	mA
INPUT RESISTANCE	5	---	---	K-OHMS
OUTPUT RESISTANCE	---	3	---	K-OHMS
OPERATING TEMPERATURE	-25	---	85	°C
STORAGE TEMPERATURE	-40	---	125	°C



PIN OUT	
1	-V EXCITATION
2	+ OUTPUT SIGNAL
3	+ V EXCITATION
4	- OUTPUT SIGNAL

NOTES

1 - SPAN IS THE ALGEBRAIC DIFFERENCE BETWEEN THE OUPUT AT FULL SCALE PRESSURE AND THE OFFSET OUTPUT

TEMPERATURE ERROR IS CALCULATED WITH RESPECT TO 25°C

LINEARITY IS MEASURED AT 1/2 FULL SCALE PRESSURE USING BEST STRAIGHT LINE FIT

4 - THE OUTPUT OF THE SENSOR IS PROPORTIONAL, RATIOMETRIC, TO THE EXCITATION VOLTAGE. THE EXCITATION MAY VARY BETWEEN 3 TO 16 V<sub>dc</sub>. ALL SPECIFICATIONS WILL NOMINALLY BE CHANGED BY THE RATIO OF V<sub>EXCITATION</sub>/12.0 V<sub>dc</sub>

5 - LIMIT SOLDERING TO 315°C FOR LESS THAN 10 SECONDS


6 - PIN 1 IS IDENTIFIED BY THE DOT ON THE HOUSING AS SHOWN ON THE VARIOUS DRAWINGS

7 - APPLY PRESSURE TO PORT INDICATED ON THE DRAWINGS SHOWN


8 - SENSORS ARE OPERATIONAL OVER VACUUM PRESSURE RANGE

9 - INPUT MEDIA RESTRICTED TO DRY GASES ONLY


THE L04 LISTING HAS A TEMPERATURE SHIFT RANGE FROM 0 TO 25°C AND 25 TO 50°C



G HOUSING



GF HOUSING

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:			<input checked="" type="checkbox"/> US (inch) CUSTOMARY	<input type="checkbox"/> SI (mm) METRIC	DRAWN	TRF	02APR01	<div>Honeywell</div>			
NO PLACE .X ±.040 ±1					CHECK	SAV	02APR01				
ONE PLACE .X ±.030 ±0,4			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE					
TWO PLACE .XX ±.015 ±0,15											
THREE PLACE .XXX ±.005 ±			DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED			SIZE DWG TYPE DRAWING NAME REV <b>C I CPC GAGE SERIES CHART 1 14</b>					
ANGLES ±											
RAW MATERIAL-COMMERCIAL STANDARD			THIRD ANGLE PROJECTION								
3D PTC			ASME Y14.5M-1994			SCALE 3:1		WEIGHT		SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[CPC100GFH](#) [CPC150GFH](#) [CPC15GFH](#) [CPC30GFH](#) [CPC60GFC](#) [CPC0.3GFC](#)