

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

WA-2RV178-A2**WA-2RV178-A2**

PAGE 1 OF 1

MDRAWING
NUMBER

5

ISSUE

REPLACES

RELEASE NO. CO-34312

CHECK

REVISIONS

A	CO-73287-J	JAL	22 NOV 93
B	CO-77591	DAW	22 JUN 94
C	CO-79125	SAD	30 NOV 94
D	CO93346	DLT	27 AUG 98

CHECK

28 APR 75


75 CHECK D/W

K P K24 APR 75

FORMTEK


FO-52848-A

DRAWN



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE—2 1/2 OZ MAX
RELEASE FORCE—1/2 OZ MIN
PRETRAVEL—.625 MAX
DIFFERENTIAL TRAVEL—.109 MAX
OVERTRAVEL—.078 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P N C

UL LISTED - FILE E12252
20A-125, 250 OR 480 VAC; 10A-125 VAC "L"
1HP-125 VAC; 2HP-250 VAC
CODE L23 1/2A-125 VDC; 1/4A-250 VDC
L288
L299
L308

CE D S

20(3)A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/.04	X
ONE PLACE	X,X	0.4/.016	X,X
TWO PLACES	X,X,X	0.15/.006	X,X,X
THREE PLACES	X,X,X,X	0.08/.003	X,X,X,X
ANGLES	X,X,X	0.38/.015	X,X,X,X
		0.13/.005	

DESIGN UNITS

SI METRIC

US CUSTOMARY

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[WA-2RV178-A2](#)