


## NOTES

- 1 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 2 - CORROSION RESISTANT STEEL ENCLOSURE, PLUNGER AND ROLLER
- 3 - SWITCH SEALED PER MIL - PRF - 8805 SYMBOL 3
- 4 - BASIC SWITCHES HAVE SOLID GOLD CONTACTS
- 5 - SWITCH CURRENT LEVELS SHALL NOT BE MORE THAN 100 MILLIAMPS @ 28 VDC
- 6 - PRINT CIRCUIT DAGRAM, CATALOG LISTING, DATE CODE AND NAVAIR PART NUMBER 1534AS392-2 ON NAMEPLATE
- 7 - PLASTIC MATERIALS SHALL CONFORM TO MIL - M - 14 OR MIL - M - 24519
- 8 - 10X MIL - W - 22759/ 11-22-9 WIRE LEADS MARKED WITH CIRCUIT IDENTIFICATION AND WIRE GAGE PER MIL - W - 5088

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



SCALE 1.5 : 1

DO NOT SCALE PRINT

### CHARACTERISTICS

OPERATING FORCE	3 ± 1 LBS
FULL OVERTRAVEL FORCE	7 LBS MAX
RELEASE FORCE	.5 LBS MIN
PRETRAVEL	.040 MAX
DIFFERENTIAL TRAVEL	.020 MAX
OVERTRAVEL	.125 MIN

## ELECTRICAL DATA

CONTACT ARRANGEMENT

3X SPDT

LOAD

28VDC  $\triangle 5$

50,000 FEET

RES

1

1

IND

## ANGLES

WEIGHT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[ML-1376](#)