



ELPAC FWA065 SERIES CLASS I

72 Watt
ITE Desktop Power Supply

- Safety Approval - IEC62368-1 Class I
- High Efficiency: Level VI
- High Power Density 4.9W/in³
- Lifetime Expectation >5 years
- Hold-up Time >20ms at full load
- Grounded Output
- 5-Year Limited Warranty



INPUT	
Input Voltage	85 – 264VAC (100 – 240VAC Nominal)
Input Frequency	47 – 63Hz (50-60Hz Rated)
Input Current	1.6A-0.8A rms
Inrush Current	<60A at 230VAC cold start
Power Factor	N/A
Zero Load Power	<0.15W
Earth Leakage Current (Typical)	N/A
Touch Leakage Current	<0.25mA@264Vac 60Hz (typical) --- Accessible parts and circuits not connected to PE

OUTPUT	
Output Voltage	See Table
Total Regulation	±5%
Minimum Load	No minimum load required
Start-Up Delay	<1.5s
Hold-Up Time	>20ms at any input voltage of full load
Ripple & Noise	<1% pk-pk **
Over Voltage Protection	110 – 135%
Over Temperature Protection	Active - Recoverable; Passive - Non recoverable
Over Current Protection	120 – 180%
Short Circuit Protection	Shutdown, auto-restart (hiccup mode)

Notes

**Ripple and noise measured with 20MHz bandwidth; 10µF tantalum capacitor in parallel with a 0.1µF ceramic capacitor.

Model Number	Output Voltage	Output Current	Peak Current ¹	Total Regulation ²	Typical Efficiency ³
FWA065012A-11A	12.0V	6.0A	7.2A	±5%	88%
FWA065015A-11A	15.0V	4.8A	5.7A	±5%	89%
FWA065018A-11A	18.0V	4.0A	4.8A	±5%	90%
FWA065024A-11A	24.0V	3.0A	3.6A	±5%	91%

Notes

1) Maximum peak load (86W) lasting 500ms with a maximum 10% duty cycle.

2) Includes initial setting, line regulation, load regulation, and thermal drift.

3) Typical at 115VAC (including output cable).

4) AC cord not included-AC cord part number 67400-185-EB can be ordered separately.

ELPAC FWA065 SERIES CLASS I

72 Watt
ITE Desktop Power Supply

inventus™
POWER

General

Efficiency	Avg. Efficiency 88.0% @ 115VAC*; Avg. Efficiency 89.0% @ 230VAC*;
MTBF	min. 200,000 hours, SR-332 issue 3
Size	5.02" (127.6mm) x 2.20" (55.9mm) x 1.37" (34.8mm)
Weight	1.3 LBS (0.59 Kg)
Power Density	4.9W/in ³

Environmental

Operating Temperature	0–60°C (Full load to 40°C, derate linearly to 50% load at 60°C)
Storage Temperature	-40°C to +85°C
Relative Humidity	5-93%, non-condensing
Cooling	Natural Convection
Vibration	Unites meet MIL-STD-810G Figure 514.6C-1 category 4

EMC & Safety


Emissions	FCC class B, EN55035:2017 EN55032:2015+A11:2020
Immunity	EN61000-4-2, -3, -4, -5, -6, -11
Certified by TUV to the following:	cTUVus
	UL62368-1:2014
	CAN/CSA-22.2 No.62368-1-14
	CB per IEC 62368-1:2014
	DOE EPS Energy efficiency (Level VI), EU CoC Energy efficiency (Level VI), EU ErP directive
	CE marked to LVD and CE EMC

Input & Output Configuration


Standard Input Cable	Not Provided Separately (P/N 67400-185-EB)
Connection on Power Supply Body	IEC 320 C14 Receptacle
Standard Output Cable	4ft for 9V 6ft for 12V, 15V, 18V, 24V
Output Cable Cord Size	2x16awg
Output Cable Connector	Switchcraft DIN-5, P/N 05GM5MX(male pins)
Output Cable Mating Connector	Switchcraft 57GB5FX (5 pin) or equivalent

Output Pin Assignments

Pin 1	Return
Pin 2	Return
Pin 3	+V1
Pin 4	Return
Pin 5	+V1



Mechanical Drawing



MWA065-Class I-DWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Inventus Power:](#)

[FWA065015A-11A](#) [FWA065012A-11A](#) [FWA065024A-11A](#)