



ELPAC MWC100 SERIES CLASS I

100 Watt
Medical Desktop Power Supply

- Medical Approval - EN60601-1 Class I 3.1 Edition
- EMC safety - IEC/EN 60601-1-2 4th edition
- Low Leakage Current
- High Efficiency: Level VI
- High Power Density 4.2W/in³
- Lifetime Expectation >5 years
- LED Indicator
- 5-Year Limited Warranty



INPUT	
Input Voltage	85 – 264VAC (100 – 240VAC Nominal)
Input Frequency	47 – 63Hz (50-60Hz Rated)
Input Current	1.5-0.6 Arms
Inrush Current	<60A at 230VAC cold start
Power Factor	>0.97
Zero Load Power	<0.15W
Earth Leakage Current (Typical)	<150µA @ 132VAC @ 60Hz
	<300µA @ 264VAC @ 60Hz
Touch Leakage Current	<50µA @ 132VAC @ 60Hz
	<100µA @ 264VAC @ 60Hz

OUTPUT	
Output Voltage	See Table
Total Regulation	±5%
Minimum Load	No minimum load required
Start-Up Delay	<1.5s
Hold-Up Time	>25ms at any input voltage of full load
Ripple & Noise	<1% pk-pk **
Over Voltage Protection	110 – 135%
Over Temperature Protection	Active - Recoverable;
Over Current Protection	115 – 175%
Short Circuit Protection	Shutdown, auto-restart (hiccup mode)

Notes

**Ripple and noise measured with 20MHz bandwidth; 10µF tantalum capacitor in parallel with a 0.1µF ceramic capacitor.

Model Number	Output Voltage	Output Current	Peak Current ¹	Total Regulation ²	Typical Efficiency ³
MWC100012A-12A	12.0V	8.3A	10.0A	±5%	89%
MWC100015A-12A	15.0V	6.6A	8.0A	±5%	90%
MWC100018A-11A	18.0V	5.5A	6.7A	±5%	90%
MWC100024A-11A	24.0V	4.1A	5.0A	±5%	90%
MWC100048A-11A	48.0V	2.08A	2.5A	±5%	91%

Notes

1) Maximum peak load (120W) lasting 500ms with a maximum 10% duty cycle.

2) Includes initial setting, line regulation, load regulation, and thermal drift.

3) Typical at 115VAC (including output cable).

4) AC cord not included-AC cord part number 67400-185-EB can be ordered separately.

ELPAC MWC100 SERIES CLASS I

100 Watt
Medical Desktop Power Supply

inventusTM
POWER

General

Efficiency	Avg. Efficiency 89.0% @ 115VAC; Avg. Efficiency 90.0% @ 230VAC;
MTBF	min. 200,000 hours, SR-332 issue 3
Size	7.09" (180.2mm) x 2.27" (57.5mm) x 1.52" (38.6mm)
Weight	1.52 LBS (0.69 Kg)
Power Density	4.2W/in ³

Environmental

Operating Temperature	0–60°C (Full load to 40°C, derate linearly to 50% load at 60°C)
Storage Temperature	-40°C to +85°C
Relative Humidity	5-95%, non-condensing
Cooling	Natural Convection
Vibration	Unites meet MIL-STD-810G Figure 514.6C-1 category 4

EMC & Safety

Emissions	FCC class B, CISPR11 class B IEC/EN60601-1-2(Ed.4) EN61000-3-2, -3
Immunity	EN61000-4-2, -3, -4, -5, -6, -11
Certified by TUV to the following:	cTUVus
	ANSI/AAMI ES60601-1:2005+A2+A1
	CAN/CSA-C22.2 No.60601-1:14
	CB per IEC60601-1 3.1 Edition
	CE marked to LVD and CE EMC /CCC

Input & Output Configuration

Standard Input Cable	Not Provided Separately (P/N 67400-185-EB)
Connection on Power Supply Body	IEC 320 C14 Receptacle
Standard Output Cable	4ft for 12V 6ft for 15V, 18V, 24V, 48V
Output Cable Cord Size	4x18awg (12V, 15V, 18V, 24V, 48V)
Output Cable Connector	Switchcraft DIN-8, P/N 15BL8M Switchcraft DIN-5, P/N 05GM5MX
Output Cable Mating Connector	Switchcraft 62GB8FX(8 pin) or equivalent(12V, 15V) Switchcraft 57GB5FX (5 pin) or equivalent(18V, 24V, 48V)


Output Pin Assignments

Pin 1	+V1
Pin 2	+V1
Pin 3	Return
Pin 4	+V1
Pin 5	Return
Pin 6	+V1
Pin 7	Return
Pin 8	Return




Output Pin Assignments

Pin 1	Return
Pin 2	Return
Pin 3	+V1
Pin 4	Return
Pin 5	+V1



Mechanical Drawing



MWC100-DWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Inventus Power:](#)

[MWC100024A-11A](#) [MWC100015A-12A](#) [MWC100012A-12A](#) [MWC100018A-12A](#) [MWC100024A-12A](#) [MWC100018A-11A](#)