


X-Coil

Gate and Signal Transformer




Features

- Small Footprint
- Low Profile
- Flat Top Surface Suitable for Pick-and-Place
- RoHS Compliant


Applications

- Gate Drive Transformer
- Isolated Pulse and Signal Transformers
- DC/DC and AC/DC Converters

Top View




Side View



Schematic



Footprint



units: mm

Electrical Specifications

Part No.	L_s^1 (uH Min.)	L_{LKG}^1 (nH Max.)	DCR (mOhms Max.)	E-T (V-uSec)	Turns Ratio	Hi-Pot (V _{DC})
XT01	100	150	320	10.0	1:1	2,250
XT02	140	150	350	12.8	1:1	120
XT03	31	600	120	3.75	1:1	2,350
XT04	86	100	140	6.25	1:1	2,350

Notes:

1. Tested at 100kHz, 0.1Vrms.
2. Electrical specifications at 25°C.
3. Operating range: -40°C to +130°C. This is a combination of ambient plus temperature rise.
4. All products are RoHS-compliant.



Specifications subject to change without notice.

800.729.2099 tel

www.icecomponents.com

[12/09] X-Coil-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ICE Components:

[XT01](#) [XT02](#) [XT03](#) [XT04](#)