OptiMOS™ Small-Signal-Transistor

Features

- N-channel
- Enhancement mode
- Logic level
- Avalanche rated
- fast switching
- Pb-free lead-plating; RoHS compliant
- Halogen-free according to IEC61249-2-21

RoHS Halogen-Free

Product Summary

V_{DS}		60	V
$R_{DS(on),max}$	V_{GS}=10 V	3	Ω
	V_{GS}=4.5 V	4	
I_D		0.3	A

PG-SOT23



Type	Package	Tape and Reel Information	Marking	HalogenFree	Packing
2N7002	PG-SOT-23	H6327: 3000 pcs/reel	72s	Yes	Non Dry

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current	I_D	T_A=25 °C	0.30	A
		T_A=70 °C	0.24	
Pulsed drain current	$I_{D,pulse}$	T_A=25 °C	1.2	
Avalanche energy, single pulse	E_{AS}	I_D=0.3 A, R_{GS}=25 Ω	1.3	mJ
Reverse diode dv/dt	dv/dt	I_D=0.3 A, V_{DS}=48 V, di/dt=200 A/µs, $T_{j,max}$=150 °C	6	kV/µs
Gate source voltage	V_{GS}		±20	V
ESD class		JESD22-A114 (HBM)	class 0 (<250V)	
Power dissipation	P_{tot} (2)	T_A=25 °C	0.5	W
Operating and storage temperature	T_j, T_{stg}		-55 ... 150	°C
IEC climatic category; DIN IEC 68-1			55/150/56	

(1) J-STD20 and JESD22

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal characteristics						
Thermal resistance, junction - minimal footprint[2]	R_{thJA}		-	-	250	K/W
Electrical characteristics, at T_j=25 °C, unless otherwise specified						
Static characteristics						
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}= 0 V, I_D=250 µA	60	-	-	V
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=V_{GS} , I_D=250 µA	1.5	2.1	2.5	
Drain-source leakage current	$I_{D (off)}$	V_{DS}=60 V, V_{GS}=0 V, T_j=25 °C	-	-	0.1	µA
		V_{DS}=60 V, V_{GS}=0 V, T_j=150 °C	-	-	5	
Gate-source leakage current	I_{GSS}	V_{GS}=20 V, V_{DS}=0 V	-	1	10	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=4.5 V, I_D=0.25 A	-	2.0	4	Ω
		V_{GS}=10 V, I_D=0.5 A	-	1.6	3	
Transconductance	g_{fs}	$\|V_{DS}\|>2\|I_D\|R_{DS(on)max}$, I_D=0.24 A	0.2	0.36	-	S

[2] Perfomed on a 40x40mm^2 FR4 PCB with both sided Cu sense-force traces, each 1mm wide, 70 µm thick and 20mm long.

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Dynamic characteristics						
Input capacitance	C_{iss}	V_{GS}=0 V, V_{DS}=25 V, f=1 MHz	-	13	20	pF
Output capacitance	C_{oss}		-	4.1	6	
Reverse transfer capacitance	C_{rss}		-	2.0	3	
Turn-on delay time	$t_{d(on)}$	V_{DD}=30 V, V_{GS}=10 V, I_D=0.5 A, R_G=6 Ω	-	3.0	4.5	ns
Rise time	t_r		-	3.3	5	
Turn-off delay time	$t_{d(off)}$		-	5.5	9	
Fall time	t_f		-	3.1	5	
Gate Charge Characteristics						
Gate to source charge	Q_{gs}	V_{DD}=48 V, I_D=0.5 A, V_{GS}=0 to 10 V	-	0.05	0.1	nC
Gate to drain charge	Q_{gd}		-	0.2	0.4	
Gate charge total	Q_g		-	0.4	0.6	
Gate plateau voltage	$V_{plateau}$		-	4.0	-	V
Reverse Diode						
Diode continous forward current	I_S	T_A=25 °C	-	-	0.3	A
Diode pulse current	$I_{S,pulse}$		-	-	1.2	
Diode forward voltage	V_{SD}	V_{GS}=0 V, I_F=0.5 A, T_j=25 °C	-	0.96	1.2	V
Reverse recovery time	t_{rr}	V_R=30 V, I_F=0.5 A, di_F/dt=100 A/µs	-	8.5	13	ns
Reverse recovery charge	Q_{rr}		-	2.4	4	nC

1 Power dissipation

$P_{tot}=f(T_A)$



2 Drain current

$I_D=f(T_A)$; $V_{GS}\geq 10$ V



3 Safe operating area

$I_D=f(V_{DS})$; $T_A=25$ °C; $D=0$

parameter: t_p



4 Max. transient thermal impedance

$Z_{thJA}=f(t_p)$

parameter: $D=t_p/T$



5 Typ. output characteristics

$I_D=f(V_{DS})$; $T_j=25$ °C

parameter: V_{GS}



6 Typ. drain-source on resistance

$R_{DS(on)}=f(I_D)$; $T_j=25$ °C

parameter: V_{GS}



7 Typ. transfer characteristics

$I_D=f(V_{GS})$; $|V_{DS}|>2|I_D|R_{DS(on)max}$



8 Typ. forward transconductance

$g_{fs}=f(I_D)$; $T_j=25$ °C



9 Drain-source on-state resistance

$R_{DS(on)}=f(T_j)$; $I_D=0.3$ A; $V_{GS}=10$ V



10 Typ. gate threshold voltage

$V_{GS(th)}=f(T_j)$; $V_{DS}=V_{GS}$; $I_D=250$ µA

parameter: I_D



11 Typ. capacitances

$C=f(V_{DS})$; $V_{GS}=0$ V; $f=1$ MHz; $T_j=25$°C



12 Forward characteristics of reverse diode

$I_F=f(V_{SD})$

parameter: T_j



13 Avalanche characteristics

$I_{AS}=f(t_{AV})$; $R_{GS}=25\,\Omega$

parameter: $T_{j(start)}$



14 Typ. gate charge

$V_{GS}=f(Q_{gate})$; $I_D=0.5$ A pulsed

parameter: V_{DD}



15 Drain-source breakdown voltage

$V_{BR(DSS)}=f(T_j)$; $I_D=250$ µA



Package Outline:



Footprint:



Packing:



Dimensions in mm

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2008 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Infineon:

2N7002 H6327 2N7002H6327XTSA2 2N7002H6327XT EVAL40WFLYP7950VTOBO1