




ADD GLUE IN SHADING AREAR



MASTER KEYWAY




NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:


SHELL: THERMOPLASTIC, UL94 V-0.
INSERT: THERMOPLASTIC, UL94 V-0.
O-RING: SILICONE RUBBER.
SEAL GASKET: SILICONE RUBBER.
JAM NUT: ALUMINIUM ALLOY, BLACK ANODIZING.
CONTACT : COPPER ALLOY,GOLD PLATED.
CLIPS: COPPER ALLOY, TIN PLATED.

2. SPECIFICATIONS:

- 2.1, RATED CURRENT: MACHINED CONTACT 7.5A (MAX).
 - 2.2, RATED VOLTAGE: 250V(AC/DC).
 - 2.3, OPERATING TEMPERATURE: -40°C ~ 125°C.
 - 2.4, DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE@1500 VOLTS AC.
 - 2.5, INSULATION RESISTANCE: 5000 MEGOHMS MIN.
 - 2.6, IP-CLASS: IP67 AND IP69K IN THE MATED CONDITION, PANEL EXTERNAL.
 - 2.7, MATING CYCLES DURABILITY: 500 CYCLES MIN.
 - 2.8, RoHS COMPLIANT.
3. SUITABLE CONTACTS : 20# CONTACT.
4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



RECOMMEND MOUNTING HOLE



RECOMMEND PCB LAYOUT

Position number	X	Y
A	0.000	5.715
B	3.302	5.715
C	4.953	2.870
D	6.604	0.000
E	4.953	-2.870
F	3.302	-5.715
G	0.000	-5.715
H	-3.302	-5.715
J	-4.953	-2.870
K	-6.604	0.000
L	-4.953	2.870
M	-3.302	5.715
N	-1.651	2.870
P	1.651	2.870
R	3.302	0.000
S	1.651	-2.870
T	-1.651	-2.870
U	-3.302	0.000
V	0.000	0.000

KEY	PART NUMBER
N	RTS714ND19P0332
W	RTS714WD19P0332
X	RTS714XD19P0332
Y	RTS714YD19P0332
Z	RTS714ZD19P0332

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036	
1) All dimensions are in metric(mm).			
2) Tolerances are as follows:			
1 PL DEC ±0.30			
2 PL DEC ±0.15			
3) Note reference = 			
MATERIAL SPECIFICATIONS:		EcoMate Aquarius,RECEPTACLE, JAM NUT, SIZE 14,19POS,PIN	
CUSTOMER:			
THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			
PROCESS SPECIFICATIONS:			
NEXT ASSY:			
SIGNATURES		DATE	
DRAWN: JOE		MAR-13-2025	
CHECKED: ORION		MAR-13-2025	
ENGINEER:			
APPROVAL: TOMMY		MAR-14-2025	
CUSTOMER:		SIZE B TYPE C- DWG NO: RTS714*D19P0332 REVISION A3	
THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.			
PROCESS SPECIFICATIONS:			
NEXT ASSY:			
SCALE: NONE			
SHEET 1		OF 1	

TITLE: EcoMate Aquarius, RECEPTACLE, JAM NUT, SIZE 14, 19POS, PIN

DWG NO:

RTS714*D19P0332

REV: A3

SH: 1

OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RTS714ND19P0332](#)