





REV	ECN	APP'D
-	4000	JT 11/03/00
A	4239	JT 12/21/00
B	5722	JT 10/20/05
C	6476	JT 2/9/10



# NOTES:

1. MATERIALS:  
BODY: POLYETHERIMIDE PER ASTM-D5205.  
GROMMET: SILICONE BLEND ELASTOMER.  
DIODE: MIL-S-19500 (SEE TABLE)  
INTERNAL PIN CONTACT:  
COPPER ALLOY, HARD GOLD PLATE PER MIL-DTL-45204.
2. PERFORMANCE SPECIFICATION PER MIL-T-81714.  
(SUBJECT TO LIMITATIONS OF THE  
ELECTRONIC COMPONENTS)  
TEMPERATURE: -65°C TO 200°C.  
INSULATION RESISTANCE: 5000 MEGOHMS MIN AT 25°C.  
DIELECTRIC WITHSTANDING VOLTAGE:  
1500 VRMS AT SEA LEVEL,  
AND 200 VRMS AT 100,000 FT. ALTITUDE.  
CURRENT RATING: 7.5A FOR SIZE 20 CONTACTS.  
VIBRATION AND SHOCK: PER MIL-T-81714 PARA 3.5.8 & 9.
3. MODULE ACCEPTS SOCKET CONTACTS (10) M39029/22-192.
4. MODULE TO BE MOUNTED ON M81714/67 RAIL SYSTEM.

IDENTIFICATION MARKING		COMPONENT
PCD P/N	REF MIL P/N	
SJE020001	M81714/62-20BT	JANTX1N5552
SJE020008	M81714/62-20BP	JANTX1N5550
SJE020009	-	JANTX1N4246
SJE020016	-	JANTX1N5618
SJE020065	-	1N5616

DIMENSIONS		TOLERANCES	PROJECTION	Amphenol Pcd SPECIFICATION DRAWING					TITLE SJE SERIES ELECTRONIC MODULE				
ANSI Y14.5M UNITS: INCHES Pro/E FILE		.XX ±0.01 .XXX ±0.005 ANGLES ±1.0°		ENGR J. TON 07/01/00									
			CHKD  2/9/10		SIZE A		DWG NO. SJE020001C		REV C				
			APPD  2/9/10		CODE: 58982		SCALE: 5:3		SHEET 1 OF 1				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SJE020053](#) [SJE020008](#) [SJE020045](#) [SJE020025](#) [SJE020016](#)