




SIGN	DATE	DESCRIPTION	APPROVER
△	03/04`14	update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			





Material:

- Item a Terminal(housing): Thermoplastic,UL 94 - V0.
- Item b Male contact pin: Copper, Gold plated

Electrical: cULus / IEC

- Voltage rating: 300V / 1000V
- Current rating: 55A / 76A
- Withstanding Voltage: 1.6 KV / 8 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: ▽



SECTION A-A

Dimension

Dim L	$N \times 10.16 + 3.04$
Dim B	$(N-1) \times 10.16$
Dim C	$(N-1) \times 10.16$

N=Number of poles

POLES	TOL
2p-5p	±0.25
6p-8p	±0.35
9p-12p	±0.45

△ EW xx 61 x 1 xxxx G

- Solid Block
02 2Contacts
03 3Contacts
12 12Contacts
- Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)
- RoHS compliant (lead<4%)
In copper Alloy
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EW 10.16 Series 2p-12p Right-Angle (down)								
PART NO.		EWxx61x1xxxxG			DWG NO.		8EW0001			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance		
		Chen Bo 03/04`14	Chen Bo 03/04`14					UNIT: mm	X.	±0.50
				SHEET: 01/01		SCALE: NONE	X.X	±0.30		
						REV: C	X.XX	±0.10		
							X°	±1°		
				SHEET: 01/01						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[EW0461510000G](#) [EW0361510000G](#) [EW0661510000G](#) [EW0761510000G](#) [EW0861510000G](#) [EW0561510000G](#)
[EW0261510000G](#) [ET0202520000G](#) [ET0302520000G](#) [ET0402520000G](#) [ET0502520000G](#) [ET0602520000G](#)
[ET0702520000G](#) [ET0802520000G](#) [ET0902520000G](#) [ET1002520000G](#) [ET1102520000G](#) [ET1202520000G](#)
[ET1302520000G](#) [ET1402520000G](#) [ET1502520000G](#) [ET1602520000G](#) [EW0961510000G](#) [EW1061510000G](#)
[EW1161510000G](#) [EW1261510000G](#)