

1

2

3


4

5

6

7

SIGN	DATE	DESCRIPTION	APPROVER
	2011.08.18	Torque(Lb-In) is changed from 5.2 (Lb-In) to 4.4(Lb-In)	Aaron
	2011.08.18	Add is cULus	Aaron
	2011.08.18	The dimension are added	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			





DIMENSION

Dim A	Nx5.08+1.52
Dim B	(N-1)x5.08
Dim C	(N-1)x5.08

N= NUMBER OF CONCATS

Poles	Tolerance
2P-6P	±0.20
7P-12P	±0.25
13P-18P	±0.30
19P-24P	±0.40



SECTION P-P

Material:

- Item ① Clamp: Brass Ni plated
- Item ② Terminal(housing): Thermoplastic (UL94V-0)
- Item ③ Terminal(cover): Thermoplastic (UL94V-0)
- Item ④ Contact pin : Brass,Tin plated.
- Item ⑤ Terminal screw: Steel Zinc plating solt "-type M3
- Item ⑥ Terminal(track): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating:300V
- Current rating: 12A
- Wire range:
- Solid wire(AWG):12-30
- Stranded wire(AWG):12-30
- Torque(Lb-In): 4.4
- Screw:M3
- Wire strip length: 6-7 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:
- Critical dimension:

V5 xx 51 x 2 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

Color
0 Black (RAL9005)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
C Green(RAL6018/U)

G: Pb<4000ppm
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	V5 - 5.08 Series 2P-24P (W/o Flange) Dinrail holder A type					
PART NO.	V5xx51x2xxxxG			DWG NO.	8V50003	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Aaron 2011.08.18	Jacke 2009.12.29		UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV: C	X.XX ±0.10
						X° ±1°

1

2

3

4

5

6

7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>V50251520000G</u>	<u>V50351520000G</u>	<u>V50451520000G</u>	<u>V50551520000G</u>	<u>V50651520000G</u>	<u>V50751520000G</u>
<u>V50851520000G</u>	<u>V50951520000G</u>	<u>V51051520000G</u>	<u>V51151520000G</u>	<u>V51251520000G</u>	<u>V51351520000G</u>
<u>V51451520000G</u>	<u>V51551520000G</u>	<u>V51651520000G</u>	<u>V51751520000G</u>	<u>V51851520000G</u>	<u>V51951520000G</u>
<u>V52051520000G</u>	<u>V52151520000G</u>	<u>V52251520000G</u>	<u>V52351520000G</u>	<u>V52451520000G</u>	