







PERFORMANCE CHARACTERISTICS

1.5 A AT 20°C (FULLY LOADED)
 CURRENT RATING: 1 A AT 70°C (FULLY LOADED)
 RATED VOLTAGE: 500 V AC (CONT /CONT)
 OPERATING TEMPERATURE : -55°C TO 125°C
 CONTACT RESISTANCE : 20 m Ω MAX
 INSERTION FORCE: 0.75N MAX/CONT
 EXTRACTION FORCE : 0.15N MIN /CONT
 INSULATION RESISTANCE: 10 MΩ MIN

NOTES

- LEAD FREE INDICATOR :LF=LEAD FREE
- THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
- FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :B.S.A.201572.001
- THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

Material			Spec ref			
Mat code			✓	TOLERANCE		
Heat treat				1DEC +0.2 1DEC		
Plating/Finish				2DEC +0.1 2DEC		
			ANGLES ±1°HDEKEN			
Dr	01-09-99	NOTTO			size	Scale
Eng			Product family	MILLIPACS	A1	5.000
Chr			Model Name		ECN	
Appr			Model Revision		REL Level	
		title	MPACS 5+2R RA RCP CONN TYPE B	size	BSC201444056	
CAT.NO. HM2002PE108				Customer Drawing	Rev. B	
Rev.B		STATUS: Released		Printed: May 25, 2009		Sheet 1 of 1

PDM: Rev.B

STATUS: Released

Printed: May 25, 2009

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM2R02PE5108N9LF](#)