

N= Number of poles

Dim A	Nx10.16+3.04
Dim B	Nx10.16-0.16
Dim C	(N-1)x10.16


Poles	Tolerance
2P-4P	±0.25
5P-7P	±0.30
8P-10P	±0.35
11P-12P	±0.45

SIGN	DATE	DESCRIPTION	APPROVER
△	2010.05.31	Add cULus standard	Jacke
△	2011.07.04	The Voltage rating is changed from 300VAC to 600VAC	Aaron
△	2011.07.04	The Tolerance is changed	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Terminal body: Thermoplastic (UL94V-0)
- Item b Terminal cover: Thermoplastic (UL94V-0)
- Item c Terminal screw: Steel Cr3+ Zinc plating "-" slot type
- Item d Clamp: Brass, Ni plated
- Item e Male contact pin: Copper Gold plated

Electrical cULus / IEC

- △ ● Voltage rating: 600VAC / 1000VAC
- Current rating: 55A / 76A
- Solid wire: 6-20 / 0.5-16mm²
- Stranded wire: 6-20 / 0.5-16mm²
- Torque: 18 Lb-In / 1.2 N.m
- Screw: M4.5
- Wire strip length: 13-14mm
- Withstanding Voltage: 1.6KV / 8KV
- Operating temperature: -40°C to +115°C
- △ ● Safety Approval: 
- Critical dimension: ▽

PART NO. **KK xx 61 x 0 xxxx G**

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
12 12 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange (RAL2011/P)
- 4 Yellow (RAL1018/A)
- 5 Green (RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey (RAL7035/D)
- 9 White (RAL1102)
- C Green (RAL6018/U)

G: Pb<4000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request.
please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KK 10.16 Series 2p-12p				DWG NO.	8KK0001		
PART NO.	KKxx61x0xxxxG				CUST NO.			
APPROVED	CHECKED	DESIGNED	DRAWN			Tolerance		
		Aaron 2011.07.04	Kind 2008.11.26			UNIT: mm	X.	±0.50
						SCALE: NONE	X.X	±0.30
							X.XX	±0.10
							X°	±1°



SHEET: 01/01

REV.: D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[KK0261500000G](#) [KK0361500000G](#) [KK0461500000G](#) [KK0561500000G](#) [KK0661500000G](#) [KK0761500000G](#)
[KK0861500000G](#) [KK0961500000G](#) [KK1061500000G](#) [KK1161500000G](#) [KK1261500000G](#)