







Customer Information Sheet

ALL DIMENSIONS IN mm



P70-2610045R SHOWN FOR—
ILLUSTRATIVE PURPOSES ONLY.
SEE TABLE FOR PART NUMBER.

RECOMMENDED PCB LAYOUT
TOLERANCE ± 0.05 (UNLESS OTHERWISE STATED)



NOTES:

1. MATERIAL.
BARREL & PLUNGER: COPPER ALLOY
SPRING: STAINLESS STEEL
2. PLATING.
PLUNGER: GOLD OVER NICKEL
BARREL : GOLD OVER NICKEL
3. TAPE MATERIAL: PET TRANSPARENT
4. SEE TABLE 1 QUANTITY OF COMPONENT PER REEL.
5. SEE TABLE 1 FOR COMPONENTS COMPATIBLE WITH TAPE POCKET SHOWN ABOVE.
6. THIS PRODUCT IS TAPED AND REELED IN ACCORDANCE WITH EIA-481 STANDARDS.
7. SEE SHEET 3 FOR P70-2620045R AND P70-2630045R.
8. DIM'I' ILLUSTRATES THE TOTAL COMPONENT HEIGHT EXCLUDING LOCATION PEG (PICK AND PLACE CAP INCLUDED.)
9. FOR COMPLETE ELECTRICAL AND MECHANICAL SPECIFICATION SEE COMPONENT SPECIFICATION C056XX (LATEST ISSUE)

REEL DETAILS




TABLE 1: DIMENSIONS.

TABLE 1: DIMENSIONS.						
HARWIN PART NO.	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'	QTY PER REEL
P70-2600045R	3.50	2.50	3.00	2.50	5.40	1000 PCS
P70-2610045R	4.50	2.70	3.80	3.10	5.60	

FC	1	23.04.24	33949
NAME	ISS.	DATE	CN/CO

APPROVED: R.PORTLOCK

CHECKED: A.YEOMANS

DRAWN: F.CHRISPINE

ASSEMBLY DRG:

TITLE:

THROUGH HOLE SPRING
LOADED POGO PIN

DRAWING NUMBER:

P70-26X0045R

OF₃

HARWIN

www.harwin.com

TOLERANCES

X. = $\pm 1\text{mm}$
X.X = $\pm 0.50\text{mm}$
X.XX = $\pm 0.20\text{mm}$
X.XXX = $\pm 0.01\text{mm}$

ANGLES = $\pm 5^\circ$
UNLESS STATED

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

MATERIAL:

SEE NOTE 1

OF₃

Customer Information Sheet




IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION


ALL DIMENSIONS IN mm



FINISHED REELING DIRECTION.

P70-2600045R SHOWN FOR ILLUSTRATIVE PURPOSES ONLY. SEE TABLE FOR PART NUMBER.

RECOMMENDED PCB LAYOUT TOLERANCE ± 0.05 (UNLESS OTHERWISE STATED)



- NOTES:
10. MATERIAL
BARREL & PLUNGER: COPPER ALLOY
SPRING: STAINLESS STEEL
 11. PLATING
PLUNGER: GOLD OVER NICKEL
BARREL : GOLD OVER NICKEL
 12. MATERIAL: PET TRANSPARENT
 13. SEE TABLE FOR QUANTITY OF COMPONENT PER REEL.
 14. THIS PRODUCT IS TAPED AND REELED IN ACCORDANCE WITH EIA-481 STANDARDS.
 15. SEE TABLE 2 FOR COMPONENTS COMPATIBLE WITH TAPE POCKET SHOWN ABOVE.
 16. DIM'E' ILLUSTRATES THE TOTAL COMPONENT HEIGHT EXCLUDING LOCATION PEG (PICK AND PLACE CAP INCLUDED.)
 17. FOR COMPLETE ELECTRICAL AND MECHANICAL SPECIFICATION SEE COMPONENT SPECIFICATION C056XX (LATEST ISSUE)

TABLE 2: DIMENSIONS.						
HARWIN PART NO.	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'	QTY PER REEL
P70-2620045R	5.50	2.70	4.80	4.10	6.90	1100 PCS
P70-2630045R	6.50	5.05	5.80	5.10	7.30	

HARWIN

www.harwin.com

TOLERANCES
X. = $\pm 1\text{mm}$
X.X = $\pm 0.50\text{mm}$
X.XX = $\pm 0.20\text{mm}$
X.XXX = $\pm 0.01\text{mm}$
ANGLES = $\pm 5^\circ$
UNLESS STATED

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

MATERIAL:

SEE NOTE 8

TITLE:
**THROUGH HOLE SPRING
LOADED POGO PIN**

DRAWING NUMBER:
P70-26X0045R

SHT
3
OF
3

FC	1	23.04.24	33949
NAME	ISS.	DATE	CN/CO
APPROVED: R.PORTLOCK			
CHECKED: A.YEOMANS			
DRAWN: F.CHRISPINE			
ASSEMBLY DRG:			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Harwin:](#)

[P70-2620045R](#) [P70-2600045R](#) [P70-2610045R](#) [P70-2630045R](#)