







Customer Information Sheet





SPECIFICATIONS:
FINISH:
4µ MIN 100% TIN OVER 2µ MIN NICKEL
ELECTRICAL:
CURRENT RATING = 3.5A
CONTACT RESISTANCE = 20mΩ MAX
ENVIRONMENTAL:
OPERATING TEMPERATURE = -55°C TO +125°C



NOTES:
1. QUANTITY OF COMPONENTS PER REEL = 3000.

RECOMMENDED PCB LAYOUT



SB	I	02.04.15	12882
NAME	ISS.	DATE	C/NOTE
APPROVED:		S.BENNETT	
CHECKED:		M.PLESTED	
DRAWN:		S.BENNETT	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
BRASS
0.20mm THICK
FINISH: SEE ABOVE
S/AREA: 8.52 mm²

TITLE:
SMT TEST TERMINAL
DRAWING NUMBER:
S2761-46R
SHT 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[S2751-46R](#) [S2761-46R](#)