

"Stay Connected" with

HEYCO®

Solar Power Components

a PennEngineering® Company



Modular Wire Routing Clips:

- Plug and Play various wire management designs.
- Mount with Straight and 90° orientation to the mounting surface for flexibility from project to project.
- Nylon 6/6 wire management devices insulate cables from PV and Racking surfaces.
- Modular wire management devices are removable.
- Nylon material is heat stabilized and UV rated for the harsh outdoor applications in the solar market.
- Patent Pending.



Stainless Steel Mounting Clips:

- Stainless Steel PV edge clips mount onto a minimum flange depth requirement of only 10 mm and holds as tight as our popular SunRunner Series.
- Locking tabs securely fasten clips to module extrusions or other panels.
- Generous lead-in for installation without tools.
- Neatly dresses cables on PV panel frames or top rail solar racking systems up to 1/4" width.
- Constructed from corrosion resistant 304 stainless steel; not for use in marine salt water environments.
- Patent Pending.

Heyco® Modular Wire Routing Devices

BUNDLE DIAMETER RANGE	PART NO. HS/UV Black	MOUNTING CONFIGURATION	DESCRIPTION	HEIGHT C	
				in.	mm.

For Mounting to S6562 or S6564 Solar PV or Rack Mount Stainless Steel Clips

.230 - .315	5,8 - 8,0	11971	Straight	HELIOS MOD S	1.19	30,2
		11972	90 Degree	HELIOS MOD 90	.84	21,3
.29 - .44	7,4 - 11,2	15248	Straight	SBC 437 MOD S	1.09	27,7

WIRE CAPACITY


.44 x .69	11,1 x 17,5	15173	Straight	CH L-27 MOD S	1.25	31,8
		15183	90 Degree	CH L-27 MOD 90	.70	17,8
.44 x 1.00	11,1 x 25,4	15174	Straight	CH L-35 MOD S	1.57	39,8
		15184	90 Degree	CH L-35 MOD 90	.70	17,8
.83 x .75	21,1 x 19,1	15150	Straight	CH OF-282-48 MOD S	1.36	34,5

Modular Mounting Clips


PANEL THICKNESS RANGE		PART NO.	DESCRIPTION	WIDTH A		LENGTH B	
Minimum	Maximum			in.	mm.	in.	mm.

For Modular, Nylon Wire Routing Devices



.032	0,8	.082	2,1	S6562	PV Modular Clip – Stainless	.69	17,5	.50	12,7
.250	6,35	.250	6,35	S6564	Rack Modular Clip – Stainless	1.32	33,5		





11971



11972 (90°)



15248



Quick
Specs

Material .025" thick 304 Stainless Steel
Temperature Range -40°F (40°C) to 572°F (300°C)

Heat Stable, UV Rated Nylon 6/6 Black
-40°F (40°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[15173](#) [15184](#) [11972](#) [S6562](#) [15183](#) [15174](#) [15248](#) [15150](#) [11971](#) [S6564](#)