


## Heyco® Preassembled Cordset Components

For Heyco Application Equipment, see pages 8-59 and 8-60


### Male Padded Bridge—NEMA 5-15P





PART DATA			PART NO.	APPLICATION TOOLING*				CRIMP DIMENSIONS	
Type	Color	AWG Range		Die	Feeds	Crimp Punch	Anvil	A in.	B in.
5-15P Male Padded Bridge	Black	18-14	<b>S7568</b>	Z294	Semi-Auto*	Z318, Z291	Z290	.26	.40
	Natural	18-14	<b>S7569</b>						
	Clear	18-14	<b>S7582</b>						
5-15P Male Padded Bridge Tinned	Black	18-14	<b>S7586</b>	Z294	Semi-Auto*	Z318, Z291	Z290	.26	.40
	Natural	18-14	<b>S7588</b>						
	Clear	18-14	<b>S7587</b>						

\*Semi-Automated Terminating Equipment is available, see page 8-60.

- Heyco Padded Blades are **far less expensive** than their Full Thickness counterparts (pages 8-31 thru 8-34), yet they are functionally equivalent.
- Thinner gauge material lowers cost, yet full pad configuration meets UL power cord requirements, including **UL 1659**.
- Heyco Padded Blades utilize less brass but retain all of the strength of our Full Thickness Blades, at a **lower cost**.
- Our Padded Bridge design **accommodates existing overmolds** designed for Padded Blades.
- Automated terminating equipment is available, see page 8-60.
- See page 8-60 for wire stripper information.
- DFARS Compliant



Materials	Alloy 260 Brass (70% Cu, 30% Zn. Higher Cu content resists dezincification) Nylon 6/6
Certifications	 Recognized Component under UL File E164169 (Component Blades only)  Certified by the Canadian Standards Association File 91824
Standards	NEMA 5-15P

*Quick  
Specs*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[S7587](#) [S7586](#) [S7588](#) [S7568](#) [S7569](#) [S7582](#)