







5					6					7					8				
COUNT		DESCRIPTION OF REVISIONS			BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS			BY	CHKD	DATE					
△							.	△						.					
△							.	△						.					
△							.	△						.					



PART NO.		HRS NO.	CONTACTS		A	B	C	D	E
DF14A-	2P-1.25H(56)	CL538-0033-3-56	2		7.45	1.25	2.95	3.65	8.05
DF14A-	3P-1.25H(56)	CL538-0034-6-56	3		8.70	2.50	4.20	4.90	9.30
DF14A-	4P-1.25H(56)	CL538-0035-9-56	4		9.95	3.75	5.45	6.15	10.55
DF14A-	5P-1.25H(56)	CL538-0036-1-56	5		11.20	5.00	6.70	7.40	11.80
DF14A-	6P-1.25H(56)	CL538-0037-4-56	6		12.45	6.25	7.95	8.65	13.05
DF14A-	7P-1.25H(56)	CL538-0038-7-56	7		13.70	7.50	9.20	9.90	14.30
DF14A-	8P-1.25H(56)	CL538-0039-0-56	8		14.95	8.75	10.45	11.15	15.55
DF14A-	9P-1.25H(56)	CL538-0040-9-56	9		16.20	10.00	11.70	12.40	16.80
DF14A-	10P-1.25H(56)	CL538-0041-1-56	10		17.45	11.25	12.95	13.65	18.05
DF14A-	15P-1.25H(56)	CL538-0114-3-56	15		23.70	17.50	19.20	19.90	24.30
DF14A-	20P-1.25H(56)	CL538-0119-7-56	20		29.95	23.75	25.45	26.15	30.55
DF14A-	25P-1.25H(56)	CL538-0124-7-56	25		36.20	30.00	31.70	32.40	36.80
DF14A-	30P-1.25H(56)	CL538-0045-2-56	30		42.45	36.25	37.95	38.65	43.05



NOTE 1. LEAD CO-PLANALITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1 MAX.
 2. WHEN THIS CONNECTOR MATES WITH DF14-S-1.25C, THE MATTING LENGTH IS 7.3mm.
 3. FOR CONNECTORS, 2 OR 3 CONTACTS, SIMPLIFIED LOCK HOLE SHALL BE SET AT THE CENTER OF HOUSING.




2	BRASS	CONTACT AREA: GOLD PLATED 0.1 μ m min LEAD AREA: TIN-COPPER PLATED 1 μ m min	5	POLYESTER	CLEAR (COVER TAPE)
			4	A-PET	CLEAR (EMBOSSED CARRIER TAPE)
1	POLYAMIDE	UNDER PLATING: NICKEL PLATED 1 μ m min BE ICE, UL 94V-0	3	PHOSPHOR BRONZE	TIN-COPPER PLATED 1 μ m min UNDER PLATING: NICKEL PLATED 0.5 μ m min
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL		DRAWING NO.		PART NO. DF 14A-*P-1.25H(56)	DESIGNED <i>L. Donkanya</i>	CHECKED <i>T. Majumder</i>	APPROVED <i>T. Majumder</i>	RELEASED
		EDC3-160309-19						
SCALE		5 : 1		CODE NO.		1 / 2		
UNITS		mm		HIROSE ELECTRIC CO., LTD		CL538-		

TO				
----	--	--	--	--

COUNT		DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT		DESCRIPTION OF REVISIONS	BY	CHKD	DATE
	△						△				
	△						△				
	△						△				

PART NO.	CONTACTS	F	G	H	J	K
DF14A- 2P-1.25H(56)	2	7.5	-	16	7.85	16.4
DF14A- 3P-1.25H(56)	3	7.5	-	16	9.1	16.4
DF14A- 4P-1.25H(56)	4	11.5	-	24	10.35	24.4
DF14A- 5P-1.25H(56)	5	11.5	-	24	11.6	24.4
DF14A- 6P-1.25H(56)	6	11.5	-	24	12.85	24.4
DF14A- 7P-1.25H(56)	7	11.5	-	24	14.1	24.4
DF14A- 8P-1.25H(56)	8	11.5	-	24	15.35	24.4
DF14A- 9P-1.25H(56)	9	11.5	-	24	16.6	24.4
DF14A- 10P-1.25H(56)	10	11.5	-	24	17.85	24.4
DF14A- 15P-1.25H(56)	15	20.2	40.4	44	24.1	44.4
DF14A- 20P-1.25H(56)	20	20.2	40.4	44	30.35	44.4
DF14A- 25P-1.25H(56)	25	26.2	52.4	56	36.6	56.4
DF14A- 30P-1.25H(56)	30	26.2	52.4	56	42.85	56.4



NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS		
CODE NO. (OLD)		CL	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
DRAWING NO.		EDC3-160309-19	PART NO.				DF14A-P-1.25H(56)
SCALE							
UNITS		HIROSE ELECTRIC CO., LTD	CODE NO.		CL538-		
mm					2		

生産月日	年 月 日
CLコード	538-*****-56
品名	DF14A-*P-1.25H(56)
納入数量	1000個
納入者	ヒロセ電機株式会社

NOTE 4 1 REEL : 1000 CONNECTORS
5 AT THE BEGINNING OF THE REEL , 30 COMPONENTS SHALL BE EMPTY
6 AT THE END OF THE REEL , 20 COMPONENTS SHALL BE EMPTY .
WHEN THE TAPE WIDTH IS 44 TO 56mm , SPROCKET HOLES SHALL
BE SET ON BOTH SIDES OF REEL AS SHOWN ON THIS DRAWING .

SH

HIROSE ELECTRIC CO., LTD.

CL538-

8

7

5

1

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF14A-2P-1.25H\(56\)](#)