


## NPN Silicon AF and Switching Transistor

- For general AF applications
- High breakdown voltage
- Low collector-emitter saturation voltage
- Complementary type: BCX42 (PNP)
- Pb-free (RoHS compliant) package
- Qualified according AEC Q101



| Type  | Marking | Pin Configuration |       |       | Package |
|-------|---------|-------------------|-------|-------|---------|
| BCX41 | EKs     | 1 = B             | 2 = E | 3 = C | SOT23   |

### Maximum Ratings

| Parameter                                   | Symbol    | Value       | Unit |
|---------------------------------------------|-----------|-------------|------|
| Collector-emitter voltage                   | $V_{CEO}$ | 125         | V    |
| Collector-base voltage                      | $V_{CBO}$ | 125         |      |
| Emitter-base voltage                        | $V_{EBO}$ | 5           |      |
| Collector current                           | $I_C$     | 800         | mA   |
| Peak collector current, $t_p \leq 10$ ms    | $I_{CM}$  | 1           | A    |
| Base current                                | $I_B$     | 100         | mA   |
| Peak base current                           | $I_{BM}$  | 200         |      |
| Total power dissipation<br>$T_S \leq 79$ °C | $P_{tot}$ | 330         | mW   |
| Junction temperature                        | $T_j$     | 150         | °C   |
| Storage temperature                         | $T_{stg}$ | -65 ... 150 |      |

### Thermal Resistance

| Parameter                                | Symbol     | Value      | Unit |
|------------------------------------------|------------|------------|------|
| Junction - soldering point <sup>1)</sup> | $R_{thJS}$ | $\leq 215$ | K/W  |

<sup>1)</sup>For calculation of  $R_{thJA}$  please refer to Application Note AN077 (Thermal Resistance Calculation)


**Electrical Characteristics** at  $T_A = 25^\circ\text{C}$ , unless otherwise specified

| Parameter                                                                                                                                                                        | Symbol        | Values         |             |             | Unit          |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|----------------|-------------|-------------|---------------|
|                                                                                                                                                                                  |               | min.           | typ.        | max.        |               |
| DC Characteristics                                                                                                                                                               |               |                |             |             |               |
| Collector-emitter breakdown voltage<br>$I_C = 10\text{ mA}, I_B = 0$                                                                                                             | $V_{(BR)CEO}$ | 125            | -           | -           | V             |
| Collector-base breakdown voltage<br>$I_C = 100\text{ }\mu\text{A}, I_E = 0$                                                                                                      | $V_{(BR)CBO}$ | 125            | -           | -           |               |
| Emitter-base breakdown voltage<br>$I_E = 10\text{ }\mu\text{A}, I_C = 0$                                                                                                         | $V_{(BR)EBO}$ | 5              | -           | -           |               |
| Collector-base cutoff current<br>$V_{CB} = 100\text{ V}, I_E = 0$<br>$V_{CB} = 100\text{ V}, I_E = 0, T_A = 150\text{ }^\circ\text{C}$                                           | $I_{CBO}$     | -<br>-         | -<br>-      | 0.1<br>20   | $\mu\text{A}$ |
| Collector-emitter cutoff current<br>$V_{CE} = 100\text{ V}, T_A = 85\text{ }^\circ\text{C}$<br>$V_{CE} = 100\text{ V}, T_A = 125\text{ }^\circ\text{C}$                          | $I_{CEO}$     | -<br>-         | -<br>-      | 10<br>75    |               |
| Emitter-base cutoff current<br>$V_{EB} = 4\text{ V}, I_C = 0$                                                                                                                    | $I_{EBO}$     | -              | -           | 100         |               |
| DC current gain <sup>1)</sup><br>$I_C = 100\text{ }\mu\text{A}, V_{CE} = 1\text{ V}$<br>$I_C = 100\text{ mA}, V_{CE} = 1\text{ V}$<br>$I_C = 200\text{ mA}, V_{CE} = 1\text{ V}$ | $h_{FE}$      | 25<br>63<br>40 | -<br>-<br>- | -<br>-<br>- | -             |
| Collector-emitter saturation voltage <sup>1)</sup><br>$I_C = 300\text{ mA}, I_B = 30\text{ mA}$                                                                                  | $V_{CEsat}$   | -              | -           | 0.9         | V             |
| Base emitter saturation voltage <sup>1)</sup><br>$I_C = 300\text{ mA}, I_B = 30\text{ mA}$                                                                                       | $V_{BEsat}$   | -              | -           | 1.4         |               |
| AC Characteristics                                                                                                                                                               |               |                |             |             |               |
| Transition frequency<br>$I_C = 20\text{ mA}, V_{CE} = 5\text{ V}, f = 20\text{ MHz}$                                                                                             | $f_T$         | -              | 100         | -           | MHz           |
| Collector-base capacitance<br>$V_{CB} = 10\text{ V}, f = 1\text{ MHz}$                                                                                                           | $C_{cb}$      | -              | 12          | -           | pF            |


<sup>1)</sup>Pulse test:  $t < 300\mu\text{s}$ ;  $D < 2\%$

**DC current gain  $h_{FE} = f(I_C)$** 


$$V_{CE} = 1 \text{ V}$$


**Collector-emitter saturation voltage**


$$I_C = f(V_{CEsat}), h_{FE} = 10$$


**Base-emitter saturation voltage**

$$I_C = f(V_{BEsat}), h_{FE} = 10$$



**Collector current  $I_C = f(V_{BE})$** 

$$V_{CE} = 1 \text{ V}$$




**Collector cutoff current**  $I_{CBO} = f(T_A)$

$V_{CBO} = 80 \text{ V}$




**Transition frequency**  $f_T = f(I_C)$

$V_{CE} = 5 \text{ V}$




**Collector-base capacitance**  $C_{cb} = f(V_{CB})$

**Emitter-base capacitance**  $C_{eb} = f(V_{EB})$





**Total power dissipation**  $P_{tot} = f(T_S)$




## Permissible Pulse Load

$$P_{\text{totmax}}/P_{\text{totDC}} = f(t_p)$$






## Foot Print



The diagram shows a top-down view of a BCW66 LED package. It is a rectangular component with four pins. The top pin is labeled 'Pin 1'. The package has a central rectangular area with the text 'EHS' and '65' (representing the date code 2005, June) printed on it. The Infineon logo is visible in the top right corner. Labels with leader lines point to the Infineon logo (Manufacturer), the date code (Date code (YM)), and the BCW66 text (Type code).

Reel ø180 mm = 3.000 Pieces/Reel  
Reel ø330 mm = 10.000 Pieces/Reel



**Edition 2009-11-16**

**Published by  
Infineon Technologies AG  
81726 Munich, Germany**

**© 2009 Infineon Technologies AG  
All Rights Reserved.**

### **Legal Disclaimer**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

### **Information**

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office ([<www.infineon.com>](http://www.infineon.com)).

### **Warnings**

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[BCX41E6327HTSA1](#)