


BGA123N6

Ultra Low Current Low Noise Amplifier for GNSS Applications

Features

- Operation frequencies: 1550 to 1615 MHz
- Ultra low current consumption: 1.3 mA
- Wide supply voltage range: 1.1 V to 3.3 V
- High insertion power gain: 19.0 dB
- Low noise figure: 0.75 dB
- 2 kV HBM ESD protection (including AI pin)
- Ultra small and RoHS/WEEE compliant package




Potential Application

The BGA123N6 is designed to enhance GNSS signal sensitivity especially in wearables and mobile cellular IoT applications. With the very good performance it ensures high system sensitivity. The ultra low power consumption of 1.5mW preserves valuable battery power, ideal for small battery powered GNSS devices. The wide supply voltage range from 1.1 V to 3.3 V ensure flexible design and high compatibility. It supports all GNSS systems including GPS, GLONASS, Beidou and Galileo.

Product Validation

Qualified for industrial applications according to the relevant tests of JEDEC47/20/22.

Block diagram



BGA123N6

Ultra Low Current Low Noise Amplifier for GNSS Applications


Table of Contents

Table of Contents

Table of Contents	1
1 Features	2
2 Maximum Ratings	3
3 Electrical Characteristics	4
4 Application Information	7
5 Package Information	9

Features**1 Features**

- Operation frequencies: 1550 to 1615 MHz
- Ultra low current consumption: 1.3 mA
- Wide supply voltage range: 1.1 V to 3.3 V
- High insertion power gain: 19.0 dB
- Low noise figure: 0.75 dB
- 2 kV HBM ESD protection (including AI pin)
- Only one external matching component needed
- Ultra small TSNP-6-2 leadless package (footprint: 0.7 x 1.1 mm²)
- RoHS/WEEE compliant package

**Description**

The BGA123N6 is designed to enhance GNSS signal sensitivity especially in wearables and mobile cellular IoT applications. With the very good performance it ensures high system sensitivity. The ultra low power consumption of 1.5mW preserves valuable battery power, ideal for small battery powered GNSS devices. The wide supply voltage range from 1.1 V to 3.3 V ensure flexible design and high compatibility. It supports all GNSS systems including GPS, GLONASS, Beidou and Galileo. The BGA123N6 LNA is manufactured in Infineon's patented bipolar technology.

The device has a very small size of only 0.7 x 1.1 mm² and a maximum height of 0.375 mm.

The device configuration is shown in Fig. 1.




Figure 1: BGA123N6 Block diagram

Product Name	Marking	Package
BGA123N6	6	PG-TSNP-6-2

Maximum Ratings

2 Maximum Ratings

Table 1: Maximum Ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Voltage at pin VCC	V_{CC}	-0.3	–	3.6	V	¹
Voltage at pin AI	V_{AI}	-0.3	–	0.9	V	–
Voltage at pin AO	V_{AO}	-0.3	–	$V_{CC} + 0.3$	V	–
Voltage at pin PON	V_{PON}	-0.3	–	$V_{CC} + 0.3$	V	–
Voltage at pin GND	V_{GND}	-0.3	–	0.3	V	–
Current into pin VCC	I_{CC}	–	–	9	mA	–
RF input power	P_{IN}	–	–	+25	dBm	²
Total power dissipation	P_{tot}	–	–	60	mW	–
Junction temperature	T_J	–	–	150	°C	–
Ambient temperature range	T_A	-40	–	85	°C	–
Storage temperature range	T_{STG}	-55	–	150	°C	–
ESD capability, HBM	V_{ESD_HBM}	-2000	–	+2000	V	³

¹All voltages refer to GND-Nodes unless otherwise noted²Tested at max VCC/VPON, 85°C and for 60 minutes³Human Body Model ANSI/ESDA/JEDEC JS-001 ($R = 1.5\text{ k}\Omega$, $C = 100\text{ pF}$)

Warning: Stresses above the max. values listed here may cause permanent damage to the device. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the integrated circuit. Exposure to conditions at or below absolute maximum rating but above the specified maximum operation conditions may affect device reliability and life time. Functionality of the device might not be given under these conditions.

3 Electrical Characteristics

Table 3: Electrical Characteristics at $T_A = 25\text{ }^{\circ}\text{C}$, $V_{CC} = 1.2\text{ V}$, $f = 1550\text{--}1615\text{ MHz}$

Parameter ¹	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Supply Voltage	V_{CC}	1.1	1.2	3.3	V	–
Supply Current	I_{CC}	–	1.3	1.65	mA	ON-Mode
		–	0.2	3	μA	OFF-Mode
Power on Voltage	V_{PON}	1.1	–	V_{CC}	V	ON-Mode
		0.0	–	0.4	V	OFF-Mode
Power on Current	I_{PON}	–	1.5	3	μA	ON-Mode
		–	–	1	μA	OFF-Mode
Insertion Power Gain $f = 1575\text{ MHz}$	$ S_{21} ^2$	16.7	18.7	20.7	dB	ON-Mode
Noise Figure ² $f = 1575\text{ MHz}$ $Z_S = 50\Omega$	NF	–	0.80	1.20	dB	ON-Mode
Input return loss ³ $f = 1575\text{ MHz}$	RL_{IN}	9	12	–	dB	ON-Mode
Output return loss ³ $f = 1575\text{ MHz}$	RL_{OUT}	10	18	–	dB	ON-Mode
Reverse isolation ³ $f = 1575\text{ MHz}$	$1/ S_{21} ^2$	25	40	–	dB	ON-Mode
Power up settling time ^{4 5}	t_S	–	8	11	μs	OFF- to ON-Mode
Inband input 1dB-compression point ³ $f = 1575\text{ MHz}$	IP_{1dB}	-23	-19	–	dBm	ON-Mode
Inband input 3rd-order intercept point ^{3 6}	IIP_3	-18	-13	–	dBm	ON-Mode
Out of band input 3rd-order intercept point ^{5 7}	IIP_{3OoB}	-14	-9	–	dBm	ON-Mode
Stability ⁵	k	>1	–	–		$f=20\text{ MHz--}10\text{ GHz}$

¹Based on application described in chapter 4²PCB losses are substrated³Verification based on AQL; not 100% tested in production⁴LNA gain changed to 90% of final gain value (in dB)⁵Guaranteed by device design; not tested in production⁶Inband @ 1575 MHz, Input power = -30 dBm for each tone, 1 MHz tone distance⁷ $f_1 = 1712.7\text{ MHz}$, $f_2 = 1850\text{ MHz}$, Input power = -20 dBm for each tone

Electrical Characteristics

Table 4: Electrical Characteristics at $T_A = 25\text{ }^{\circ}\text{C}$, $V_{CC} = 1.8\text{ V}$, $f = 1550\text{--}1615\text{ MHz}$

Parameter ¹	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Supply Voltage	V_{CC}	1.1	1.8	3.3	V	–
Supply Current	I_{CC}	–	1.35	1.7	mA	ON-Mode
		–	0.2	3	μA	OFF-Mode
Power on Voltage	V_{PON}	1.1	–	V_{CC}	V	ON-Mode
		0.0	–	0.4	V	OFF-Mode
Power on Current	I_{PON}	–	3	6	μA	ON-Mode
		–	–	1	μA	OFF-Mode
Insertion Power Gain $f = 1575\text{ MHz}$	$ S_{21} ^2$	17.0	19.0	21.0	dB	ON-Mode
Noise Figure ² $f = 1575\text{ MHz}$ $Z_S = 50\Omega$	NF	–	0.75	1.15	dB	ON-Mode
Input return loss ³ $f = 1575\text{ MHz}$	RL_{IN}	9	12	–	dB	ON-Mode
Output return loss ³ $f = 1575\text{ MHz}$	RL_{OUT}	10	17	–	dB	ON-Mode
Reverse isolation ³ $f = 1575\text{ MHz}$	$1/ S_{21} ^2$	25	40	–	dB	ON-Mode
Power up settling time ^{4 5}	t_S	–	7	10	μs	OFF- to ON-Mode
Inband input 1dB-compression point ³ $f = 1575\text{ MHz}$	IP_{1dB}	-19	-15	–	dBm	ON-Mode
Inband input 3rd-order intercept point ^{3 6}	IIP_3	-17	-12	–	dBm	ON-Mode
Out of band input 3rd-order intercept point ^{5 7}	IIP_{3OoB}	-12	-7	–	dBm	ON-Mode
Stability ⁵	k	>1	–	–		$f=20\text{ MHz--}10\text{ GHz}$

¹Based on application described in chapter 4²PCB losses are substrated³Verification based on AQL; not 100% tested in production⁴LNA gain changed to 90% of final gain value (in dB)⁵Guaranteed by device design; not tested in production⁶Inband @ 1575 MHz, Input power = -30 dBm for each tone, 1 MHz tone distance⁷ $f_1 = 1712.7\text{ MHz}$, $f_2 = 1850\text{ MHz}$, Input power = -20 dBm for each tone

Electrical Characteristics

Table 5: Electrical Characteristics at $T_A = 25\text{ }^{\circ}\text{C}$, $V_{CC} = 2.8\text{ V}$, $f = 1550\text{--}1615\text{ MHz}$

Parameter ¹	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Supply Voltage	V_{CC}	1.1	2.8	3.3	V	–
Supply Current	I_{CC}	–	1.45	1.8	mA	ON-Mode
		–	0.2	3	μA	OFF-Mode
Power on Voltage	V_{PON}	1.1	–	V_{CC}	V	ON-Mode
		0.0	–	0.4	V	OFF-Mode
Power on Current	I_{PON}	–	5	10	μA	ON-Mode
		–	–	1	μA	OFF-Mode
Insertion Power Gain $f = 1575\text{ MHz}$	$ S_{21} ^2$	17.2	19.2	21.2	dB	ON-Mode
Noise Figure ² $f = 1575\text{ MHz}$ $Z_S = 50\Omega$	NF	–	0.75	1.15	dB	ON-Mode
Input return loss ³ $f = 1575\text{ MHz}$	RL_{IN}	9	12	–	dB	ON-Mode
Output return loss ³ $f = 1575\text{ MHz}$	RL_{OUT}	10	17	–	dB	ON-Mode
Reverse isolation ³ $f = 1575\text{ MHz}$	$1/ S_{21} ^2$	25	30	–	dB	ON-Mode
Power up settling time ^{4 5}	t_S	–	7	10	μs	OFF- to ON-Mode
Inband input 1dB-compression point ³ $f = 1575\text{ MHz}$	IP_{1dB}	-16	-12	–	dBm	ON-Mode
Inband input 3rd-order intercept point ^{3 6}	IIP_3	-16	-11	–	dBm	ON-Mode
Out of band input 3rd-order intercept point ^{5 7}	IIP_{3OoB}	-11	-6	–	dBm	ON-Mode
Stability ⁵	k	>1	–	–		$f=20\text{ MHz--}10\text{ GHz}$

¹Based on application described in chapter 4²PCB losses are substrated³Verification based on AQL; not 100% tested in production⁴LNA gain changed to 90% of final gain value (in dB)⁵Guaranteed by device design; not tested in production⁶Inband @ 1575 MHz, Input power = -30 dBm for each tone, 1 MHz tone distance⁷ $f_1 = 1712.7\text{ MHz}$, $f_2 = 1850\text{ MHz}$, Input power = -20 dBm for each tone

4 Application Information

Pin Configuration and Function




Figure 2: BGA123N6 Pin Configuration (top view)

Table 6: Pin Definition and Function

Pin No.	Name	Function
1	GND	Ground
2	VCC	DC Supply
3	AO	LNA Output
4	GND	Ground
5	AI	LNA Input
6	PON	Power On Control

BGA123N6

Ultra Low Current Low Noise Amplifier for GNSS Applications

Application Information

Application Board Configuration




Figure 3: BGA123N6 Application Schematic

Table 7: Bill of Materials Table

Name	Value	Package	Manufacturer	Function
C1 (optional)	1nF	0402	Various	DC block ¹
C2 (optional)	$\geq 1\text{nF}$	0402	Various	RF bypass ²
L1	10nH	0402	Murata LQW15 type	Input matching
N1	BGA123N6	PG-TSMP-6-2	Infineon	GNSS LNA

¹DC block might be realized with pre-filter in GNSS applications.

²RF bypass recommended to mitigate power supply noise.

BGA123N6

Ultra Low Current Low Noise Amplifier for GNSS Applications

Package Information

5 Package Information




Figure 4: PG-TSNP-6-2 Package Outline (0.7mm x 1.1mm x 0.375mm)




Figure 5: Footprint Recommendation

BGA123N6

Ultra Low Current Low Noise Amplifier for GNSS Applications

Package Information




Figure 6: Marking Specification (top view)

Table 8: Monthly Date Code Marking

Month	2015	2016	2017	2018	2019	2020	2021	2022	2023	2024	2025	2026
1	a	p	A	P	a	p	A	P	a	p	A	P
2	b	q	B	Q	b	q	B	Q	b	q	B	Q
3	c	r	C	R	c	r	C	R	c	r	C	R
4	d	s	D	S	d	s	D	S	d	s	D	S
5	e	t	E	T	e	t	E	T	e	t	E	T
6	f	u	F	U	f	u	F	U	f	u	F	U
7	g	v	G	V	g	v	G	V	g	v	G	V
8	h	x	H	X	h	x	H	X	h	x	H	X
9	j	y	J	Y	j	y	J	Y	j	y	J	Y
10	k	z	K	Z	k	z	K	Z	k	z	K	Z
11	l	2	L	4	l	2	L	4	l	2	L	4
12	n	3	N	5	n	3	N	5	n	3	N	5




Figure 7: PG-TSnp-6-2 Carrier Tape

Revision History

-

Page or Item	Subjects (major changes since previous revision)
---------------------	---

Revision 2.1, 2021-02-22**Revision History**

7	Figure 2 changed to top view

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2021-02-22

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2021 Infineon Technologies AG.

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference

Doc_Number

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party. In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications. The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[BGA123N6E6327XTSA1](#)