






Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT



RECOMMENDED PC BOARD PATTERN

- NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW Temp(°C)
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM
: IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C(60~120s)
- NOTE2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
- NOTE3. CO-PLANARITY SHALL BE 0.1 MAX
- NOTE4. PC BOARD THICKNESS=1.6
- NOTE5. RECOMMENDED SOLDER THICKNESS=0.15




MATED CONNECTORS


PACKING STYLE

1. Place connectors into an embossed carrier tape.


DIRECTION OF UNREELING



2. Put a reel into a cardboard.



W = (405) (mm)
D = (405) (mm)
H = (39) (mm)



2	BRASS	TIN PLATING			
1	PPS	BLACK	3	BRASS	TIN PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
		APPROVED : HK. UMEHARA		20201021	DRAWING NO. EDC-167736-55-00
		CHECKED : HH. TSUKUMO		20201021	PART NO. GT8E-3P-2H(55)
		DESIGNED : KK. AIHARA		20201021	CODE NO. CL758-0096-4-55
		DRAWN : KK. AIHARA		20201021	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[GT8E-3P-2H\(55\)](#)