


- Notes
- 1 The recommended tightening torque of REF.NO. ④ : 1.5N · m.
 - 2 The recommended tightening torque of REF.NO. ⑧ : 0.3 to 0.4N · m.
Loctite 243 Henkel Japan or equivalent is recommended to prevent REF.NO. ⑧ from looseing.
 - 3 Across flats of hexagon hole of REF.NO. ⑧ : 1.27.
 - 4 One example of the rotation of REF.NO. ① and ④ is shown.
 - 5 Applicable crimping tool of REF.NO. ⑨ : HR10A-TC-02<CL150-0041-2>
The hole diameter for crimping: Ø5.3
 - 6 The cable pull and twisting strength and other characteristics may differ,
depending on the cable structure, please confirm before the use.

5	Brass	Matte finish nickel plated			
4	Brass	Matte finish nickel plated	9	Brass	
3	Brass	Silver plating 3µm min.	8	Steel	Nickel plating M2.6×0.45
2	Polyamide	(Black) UL94V-0	7	Chloroprene rubber	(Black)
1	Zinc alloy	Matte finish nickel plated	6	Steel	Nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS
mm



SCALE
2 : 1

COUNT
△

DESCRIPTION OF REVISIONS

DESIGNED

CHECKED

DATE

HRS

HIROSE
ELECTRIC
CO., LTD.

APPROVED : EJ. KUNII

16. 03. 23

CHECKED : EJ. KUNII

16. 03. 23

DESIGNED : TP. KOMATSU

16. 03. 23

DRAWN : TP. KOMATSU

16. 03. 23

DRAWING
NO.

EDC-021288-73-00

PART
NO.

HR11-9BPB-4P<73>

CODE
NO.

CL111-0101-0-73

△ 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[HR11-9BPB-4P\(73\)](#)