


DRAWING FOR REFERENCE: This is subject to change without notice

In cases where the application will demand a high level of reliability, such as automotive, please contact a company representative for further information.

Applicable standard					
Rating	Operating temperature range	-40 °C to 60 °C	Storage temperature range	-40 °C to 60 °C (At packing)	
Specifications					
Item	Test method		Requirements	QT	AT
Construction					
General examination	Visually and measuring instrument.		According to drawing.	X	X
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
0					
REMARK A product corresponding to RoHS.			APPROVED	MT. SHIBUTANI	17. 07. 14
			CHECKED	FS. YOSHIDA	17. 07. 14
			DESIGNED	TY. SATO	17. 07. 14
			DRAWN	TY. SATO	17. 07. 14
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-378349-00-00
HRS	SPECIFICATION SHEET		PART NO.	MF11BMT-PC	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL709-7040-0-00	A 1/1

1		2		3		4	
A						A	
B						B	
C						C	
D						D	
E						E	
F						F	
1		Elastomer		Black			
NO.		MATERIAL		FINISH . REMARKS		NO. MATERIAL FINISH . REMARKS	
UNITS mm				SCALE 2 : 1		COUNT 	
				DESCRIPTION OF REVISIONS		DESIGNED	
						CHECKED	
						DATE	
 HIROSE ELECTRIC CO., LTD.		APPROVED :MT. SHIBUTANI		17. 07. 14		DRAWING NO. EDC-378349-00-00	
		CHECKED :FS. YOSHIDA		17. 07. 14		PART NO. MF11BMT-PC	
		DESIGNED :TY. SATO		17. 07. 14		CODE NO. CL709-7040-0-00	
		DRAWN :TY. SATO		17. 07. 14		 1/1	
FORM HC0011-5-51		2		3		4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[MF11BMT-PC](#)