




- NOTES 1. APPLICABLE CRIMPING CONTACT : JRC-SC2-212 (AWG#24 TO 20)
JRC-SC2-222 (AWG#28 TO 24)
2. APPLICABLE CRIMP CONTACT EXTRACTION TOOL : RM-TP (CL150-0008-7)
- ③ THE RECOMMENDED CLUMP TORQUE OF REF.NO.⑤ TO BE 4 TO 4.5N·m.
- ④ ACROSS FLATS OF HEXAGON HEAD OF REF.NO.⑧ TO BE 1.27mm.
- THE RECOMMENDED CLUMP TORQUE OF REF.NO.⑧ TO BE 0.3 TO 0.4N·m.
- LOCTITE 243, HENKEL JAPAN IS RECOMMENDED TO PREVENT REF.NO.⑧ FROM LOOSENING.
5. ROTATION EXAMPLES OF REF.NO.① AND ⑤ ARE SHOWN.
6. THE CABLE PULL AND TWISTING AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

4	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED	8	STEEL	NICKEL PLATING.	HEX SOCKET SET SCREW M2.6X0.45X2
3	PHOSPHOR BRONZE	NICKEL PLATING	7	BRASS	NICKEL PLATING	M3X0.5X10
2	POLYCARBONATE	(BLACK) UL94V-0	6	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED	
1	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED	5	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS	

UNITS mm		SCALE 1 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
APPROVED : EJ. KUNII 16.01.25				DRAWING NO. EDC-029006-71-00			
CHECKED : EJ. KUNII 16.01.25				PART NO. JR21PK-16SC(71)			
DESIGNED : TY. TAKAHASHI 16.01.25				CODE NO. CL114-0573-8-71			
DRAWN : TY. TAKAHASHI 16.01.25				1/1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[JR21PK-16SC\(71\)](#)