




- NOTE 1 This dimension indicates the condition after assembling to a cable.
2. When this plug is mated with receptacle, clamping torque of part No. 2 should be 1.5 to 3 N·m.
Optional plastic spanner below can be used as a substitution.

Plastic spanner	Part No.	Code No.
	MF10-T1	CL709-0205-8-00

3 Ferrules are not included in this product.
Please use MU standard ferrule below.

Inner hole diameter:mm	Part NO.	Code No.
0.125	HMUA-F3-A125(10)	CL710-0024-3-10
0.1255	HMUA-F3-A1255(10)	CL710-0121-0-10
0.126	HMUA-F3-A126(10)	CL710-0025-6-10

7	BRASS	CHROME PLATING	14	ZIRCONIA	
6	NBR RUBBER	COLOR:BLACK	13	NYLON	
5	NBR RUBBER	COLOR:BLACK	12	STAINLESS STEEL	NYELOCK
4	ZINC DIECAST	NICKEL PLATING	11	ALUMINIUM ALLOY	ANODIC OXIDE COATING
3	ALUMINIUM ALLOY	ANODIC OXIDE COATING	10	STAINLESS STEEL	
2	BRASS	CHROME PLATING	9	PPS RESIN	COLOR:BLACK
1	ZINC DIECAST	CHROME PLATING	8	NBR RUBBER	COLOR:BLACK
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT		DESCRIPTION OF REVISIONS
HRS		HIROSE ELECTRIC CO., LTD.	APPROVED : MT. SHIBUTANI		18. 02. 02
			CHECKED : FS. YOSHIDA		18. 02. 02
			DESIGNED : TY. SATO		18. 02. 02
			DRAWN : MK. INOUE		18. 02. 01
			DRAWING NO. EDC-179290-31-00		
			PART NO. MF10S-WP6C52-0200(31)		
			CODE NO. CL709-0215-1-31		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[MF10S-WP6C52-0200\(31\)](#)