



Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES 1. APPLICABLE WIRE IS AWG #16~#18. (UL1007, UL1015)
INSULATION DIAMETER ϕ 3.30mm MAX.
2. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS
(CRIMP HEIGHT etc.) WILL BE SPECIFIED ACCORDING TO
AWG # OR WIRE APPLIED.
3. ONE PACKAGE CONSISTS OF 100 PCS.
4. REFER TO ATAI-E3038 FOR CRIMP QUALITY STANDARDS.

				1	COPPER ALLOY		CONTACT AREA : GOLD PLATING 0.2μm MIN. TERMINAL AREA : TIN PLATING 1μm MIN. UNDER PLATING : NICKEL PLATING 0.5μm MIN.		
NO.	MATERIAL		FINISH , REMARKS		NO.	MATERIAL		FINISH , REMARKS	
UNITS mm			SCALE 5 : 1	 COUNT 1	DESCRIPTION OF REVISIONS DIS-E-004910		DESIGNED TY. MIURA	CHECKED NM. NISHIMATSU	DATE 14. 01. 20
 HIROSE ELECTRIC CO., LTD.			APPROVED : RI. TAKAYASU		12. 12. 11	DRAWING NO. EDC3-128191-00			
			CHECKED : AH. KODAMA		12. 12. 11	PART NO. PQ50-1618SCA			
			DESIGNED : TY. MIURA		12. 12. 10	CODE NO. CL236-2044-3-00			
			DRAWN : TY. MIURA		12. 12. 10	 1 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[PQ50-1618SCA](#)