


1			2			3			4		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS
△					△					△	
△					△					△	
△					△					△	



- NOTES
- THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑩ TO BE 0.2 TO 0.3 N·m. LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑩ FROM LOOSENING.
  - ROTATION EXAMPLES OF REF. NO. ① AND ⑥ ARE SHOWN.
  - THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

5	BRASS	NICKEL PLATING	10	BRASS	NICKEL PLATING
4	DIALYL PHTHALATE	(BLACK) UL94V-0	9	PHOSPHOR BRONZE	NICKEL PLATING JIS B 1251
3	DIALYL PHTHALATE	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING JIS B 1101 M2×10
2	COPPER ALLOY	SILVER PLATING 5μm min.	7	BRASS	NICKEL PLATING
1	BRASS	NICKEL PLATING	6	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		M. Sato	S. Komatsu	E. Kunita	M. Sato	
		07.03.30	07.04.09	07.04.10	07.04.11	
DRAWING NO. EDC4-003127-71		PART NO. RM15TP-10S(71)				
CODE NO. CL109-0055-8-71		1/1				

TO
R

SCALE  
 2 : 1

UNITS  
 mm

**HRS**

HIROSE ELECTRIC CO., LTD.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM15TP-10S\(71\)](#)