



- NOTES
- One example of the rotation of Ref. No. ⑤ to Ref. No. ① is shown.
  - The recommended torque of Ref. No. ⑤ : 2 TO 3 N·m.
  - Across flats hexagon head of Ref. No. :1.27 the recommended clamp torque of Ref. No. ⑧ : 0.3 to 0.4 N·m.
  - The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.
  - LOCTITE 243 HENKEL JAPAN or equivalent is recommended to prevent Ref. No. ①, ⑦ and ⑧ for loosening.

4	DIALYL PHTHALATE	(BLACK)	UL94V-0	8	STEEL	NICKEL PLATING	HEXAGON SOCKET SET SCREW M2. 6X0. 45X2
3	DIALYL PHTHALATE	(BLACK)	UL94V-0	7	BRASS	NICKEL PLATING	JIS B 1101 M2X0. 4X8
2	COPPER ALLOY	SILVER PLATING	2 μm min.	6	ZINC ALLOY	MATTE FINISH NICKEL PLATED	
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED		5	ZINC ALLOY	MATTE FINISH NICKEL PLATED	
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS
UNITS mm		SCALE 2 : 1	COUNT △	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED
F		APPROVED : HY. KOBAYASHI	15. 10. 27	DRAWING NO.		EDC-027935-00-00	
HRS HIROSE ELECTRIC CO., LTD.		CHECKED : HY. KOBAYASHI	15. 10. 27	PART NO.		RM12BJB-3PH	
		DESIGNED : HT. ZENBA	15. 10. 26	CODE NO.		CL109-0830-3-00	
		DRAWN : HT. ZENBA	15. 10. 26			△ 1/1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM12BJB-3PH](#)