




- Notes
- 1 Shall be disassembled when delivered
 - 2 Applicable crimp contact:
Contact No. 2, 11, 12
RP17-SC-212 (Applicable cable size : AWG #18 to #22)
Cable jacket outer diameter shall be $\phi 1.7\text{mm}$ or less.
Contact No. 1, 3 to 10
RP17-SC-222 (Applicable cable size : AWG #24 to #30)
Cable jacket outer diameter shall be $\phi 1.2\text{mm}$ or less.
 - 3 Extraction tool : RP6-SC-TP
 - 4 Applicable cable crimping tool : RP17-TC-01
 - 5 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure, please confirm before the use.
 - 6 The recommended clamp torque of Ref. No. ⑥ to be $0.2\text{N} \cdot \text{m}$.

3	POLYCARBONATE	(BLACK) UL94V-0	6	BRASS	BLACK CHROMATE TREATMENT (TRIVALENT CHROMIUM)	JIS B 1111 M2×0.4×4
2	POLYCARBONATE	(BLACK) UL94V-0	5	POLYVINYLCHLORIDE	(BLACK)	
1	POLYCARBONATE	(BLACK) UL94V-0	4	BRASS		
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS	
UNITS mm						
		SCALE 2 : 1	COUNT △	DESCRIPTION OF REVISIONS		DESIGNED
						CHECKED
						DATE
HRS HIROSE ELECTRIC CO., LTD.		APPROVED	•EJ. KUNII	16. 02. 12	DRAWING NO.	EDC-026436-71-00
		CHECKED	•EJ. KUNII	16. 02. 12	PART NO.	RP17-13J-12SC(71)
		DESIGNED	•WR. AJIRO	16. 02. 12	CODE NO.	CL113-0515-5-71
		DRAWN	•WR. AJIRO	16. 02. 12		△ 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RP17-13J-12SC\(71\)](#)