






In case that the application demands a high level of reliability, such as automotive, please contact a company representative for further information.

2>1> FIG-1 CABLE ASSEMBLED CONDITION




3> TABLE-1 APPLICABLE CABLE

APPLICABLE CABLE	
CONDUCTOR DIAMETER	JACKET DIAMETER
φ 0.4	φ 1.2 (max)
φ 0.5	
φ 0.65	

NOTE

- 1> CABLE INSERTION AREA BLOCK IS TEMPORARILY FIXED AS SHOWN IN FIG-1 WHEN DELIVERED.
- 2> CABLE SHALL BE CLAMPED TO DIRECTION "P" WITH PLYER AFTER BENDED CABLE IS CUTTED BY NIPPER AS SHOWN IN FIG-1.
- 3> APPLICABLE CABLE IS SHOWN IN TABLE-1.



1	POLYAMIDE	(BLACK) UL94V-0	2	PHOSPHOR BRONZE	CONTACT AREA: TIN PLATING INSULATION DISPLACEMENT AREA: GOLD FLASH PLATING	
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS	RELEASED
CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	
		Y. Sato	T. Wto	Y. Enami	H. Mura	
		05.11.11	05.11.11	05.11.11	05.11.11	
DRAWING NO. EDC3-046857-01		PART NO. PF-2MB (50)				
SCALE 4 : 1		CODE NO. CL223-0110-9-50				
UNITS mm		HIROSE ELECTRIC CO., LTD				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[PF-2MB\(50\)](#)