



Jun.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES
1. ROTATION EXAMPLES OF REF. NO. ① AND ⑨ ARE SHOWN.
2. REF. No. ⑭ : HEX SOCKET SET SCREW (HEX : 1.27).
THE RECOMMENDED TIGHTENING TORQUE : 0.3~0.4 N · m.



7	PHOSPHOR BRONZE	SILVER PLATING	14	STAINLESS STEEL	
6	STAINLESS STEEL		13	BRASS	NICKEL PLATING
5	PHOSPHOR BRONZE	SILVER PLATING 4 μm min	12	SILICONE RUBBER	(BLACK)
4	PHOSPHOR BRONZE	SILVER PLATING 4 μm min	11	PHOSPHOR BRONZE	NICKEL PLATING
3	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0	10	SILICONE RUBBER	(BLACK)
2	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0	9	ALUMINUM ALLOY	BLACK CHROMATE TREATMENT(Cr3)
1	ALUMINUM ALLOY	BLACK CHROMATE TREATMENT(Cr3)	8	ALUMINUM ALLOY	BLACK CHROMATE TREATMENT(Cr3)
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT		DESCRIPTION OF REVISIONS
HRS		APPROVED : EJ. KUNII	13.11.26	DRAWING NO. EDC3-110226-01	
HIROSE ELECTRIC CO., LTD.		CHECKED : HY. KISHI	13.11.26	PART NO. H/MS3106A22-22S-D-T(73)	
		DESIGNED : KN. IKEHARA	13.11.22	CODE NO. CL120-0324-5-73	
		DRAWN : KN. IKEHARA	13.11.22		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[H/MS3106A22-22S-D-T\(73\)](#)