




- Notes
- 1 Rotation examples of ref. No. ⑨ to ref. No. ① is shown.
 - 2 The recommended clamp torque of ref. No. ⑨ : 3 N·m.
LOCTITE 263 HENKEL JAPAN or equivalent is recommended to prevent ref. No. ⑨ from loosening.
 - 3 This product to be used with cableclamp : JR16WCC-※(72)
※ designate diameter of applicable cable.
 - 4 The cable pull and twisting strength, waterproof tightness and other characteristics may differ,
depending on the cable structure.
Please confirm before the use.

4	PPS	(BLACK)	UL94V-0	9	ZINC ALLOY	CHROME PLATING
3	PPS	(BLACK)	UL94V-0	8	SILICONE RUBBER	(BLACK)
2	COPPER ALLOY	SILVER PLATING	2μm min.	7	BRASS	CHROME PLATING
1	ZINC ALLOY	CHROME PLATING		6	SILICONE RUBBER	(RED)
				5	POLYACETAL	(WHITE)
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		2 : 1		1	DIS-C-00000841	KN. IKEHARA	HY. KOBAYASHI

 HIROSE ELECTRIC CO., LTD.	APPROVED	HY. KOBAYASHI	15. 11. 06	DRAWING NO.	EDC-111152-81-00	
	CHECKED	HY. KOBAYASHI	15. 11. 06	PART NO.	RM15WTPZA-4S(81)	
	DESIGNED	KN. IKEHARA	15. 11. 06	CODE NO.	CL109-1730-4-81	
	DRAWN	KN. IKEHARA	15. 11. 06			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM15WTPZA-4S\(81\)](#)