

MOSFET

OptiMOS™ P3 Power-Transistor, -30 V

Features

- single P-Channel in S3O8
- Qualified according JEDEC¹⁾ for target applications
- 150 °C operating temperature
- V_{GS}=25 V, specially suited for notebook applications
- Pb-free; RoHS compliant
- applications: battery management, load switching
- Halogen-free according to IEC61249-2-21





Table 1 Key Performance Parameters

Parameter	Value	Unit
V _{DS}	-30	V
R _{DS(on),max}	8.6	mΩ
I _D	-40	A



Type / Ordering Code	Package	Marking	Related Links
BSZ086P03NS3 G	PG-TSDSON-8	086P3N	-

¹⁾ J-STD20 and JESD22

Table of Contents

Description	1
Maximum ratings	3
Thermal characteristics	3
Electrical characteristics	4
Electrical characteristics diagrams	6
Package Outlines	10
Revision History	11
Trademarks	11
Disclaimer	11

1 Maximum ratings

at $T_j=25\text{ °C}$, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Continuous drain current	I_D	-	-	-40 -40 -13.5	A	$T_C=25\text{ °C}$ $T_C=70\text{ °C}$ $T_A=25\text{ °C}^{1)}$
Pulsed drain current	$I_{D,pulse}$	-	-	-160	A	$T_C=25\text{ °C}^{2)}$
Avalanche energy, single pulse	E_{AS}	-	-	105	mJ	$I_D=-20\text{ A}$, $R_{GS}=25\text{ }\Omega$
Gate source voltage	V_{GS}	-25	-	25	V	-
Power dissipation	P_{tot}	-	-	69 2.1	-	$T_A=25\text{ °C}$ $T_A=25\text{ °C}^{1)}$
Operating and storage temperature	T_j , T_{stg}	-55	-	150	°C	IEC climatic category; DIN IEC 68-1: 55/150/56
ESD class	-	-	1C	-	-	(1kV-2kV), JESD22-A114 HBM
Soldering temperature	-	-	260	-	°C	-

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	1.8	K/W	-
Thermal resistance, junction - ambient, 6 cm ² cooling area ¹⁾	R_{thJA}	-	-	60	K/W	-

¹⁾ Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.

²⁾ See Fig. 3 for more detailed information

3 Electrical characteristics

at $T_j=25\text{ °C}$, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	-30	-	-	V	$V_{GS}=0\text{ V}$, $I_D=-250\text{ A}$
Gate threshold voltage	$V_{GS(th)}$	-3.1	-2.5	-1.9	V	$V_{DS}=V_{GS}$, $I_D=-105\text{ }\mu\text{A}$
Zero gate voltage drain current	I_{DSS}	-	-	-1 -10	μA	$V_{DS}=-30\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=25\text{ °C}$ $V_{DS}=-30\text{ V}$, $V_{GS}=0\text{ V}$, $T_j=125\text{ °C}$
Gate-source leakage current	I_{GSS}	-	-	-100	nA	$V_{GS}=-25\text{ V}$, $V_{DS}=0\text{ V}$
Drain-source on-state resistance	$R_{DS(on)}$	-	6.5 8.7	8.6 13.4	m Ω	$V_{GS}=-10\text{ V}$, $I_D=-20\text{ A}$ $V_{GS}=-6\text{ V}$, $I_D=-20\text{ A}$
Gate resistance	R_G	-	2.2	-	Ω	-
Transconductance	g_{fs}	30	43	-	S	$ V_{DS} >2 I_D R_{DS(on)max}$, $I_D=-20\text{ A}$

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	3190	4785	pF	$V_{GS}=0\text{ V}$, $V_{DS}=-15\text{ V}$, $f=1\text{ MHz}$
Output capacitance	C_{oss}	-	1520	2280	pF	$V_{GS}=0\text{ V}$, $V_{DS}=-15\text{ V}$, $f=1\text{ MHz}$
Reverse transfer capacitance	C_{rss}	-	110	165	pF	$V_{GS}=0\text{ V}$, $V_{DS}=-15\text{ V}$, $f=1\text{ MHz}$
Turn-on delay time	$t_{d(on)}$	-	16	24	ns	$V_{DD}=-15\text{ V}$, $V_{GS}=-10\text{ V}$, $I_D=-20\text{ A}$, $R_{G,ext}=6\text{ }\Omega$
Rise time	t_r	-	46	69	ns	$V_{DD}=-15\text{ V}$, $V_{GS}=-10\text{ V}$, $I_D=-20\text{ A}$, $R_{G,ext}=6\text{ }\Omega$
Turn-off delay time	$t_{d(off)}$	-	35	53	ns	$V_{DD}=-15\text{ V}$, $V_{GS}=-10\text{ V}$, $I_D=-20\text{ A}$, $R_{G,ext}=6\text{ }\Omega$
Fall time	t_f	-	8	12	ns	$V_{DD}=-15\text{ V}$, $V_{GS}=-10\text{ V}$, $I_D=-20\text{ A}$, $R_{G,ext}=6\text{ }\Omega$

Table 6 Gate charge characteristics¹⁾

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	16.1	21.4	nC	$V_{DD}=-15\text{ V}$, $I_D=-20\text{ A}$, $V_{GS}=0\text{ to }-10\text{ V}$
Gate charge at threshold	$Q_{g(th)}$	-	5.0	6.7	nC	$V_{DD}=-15\text{ V}$, $I_D=-20\text{ A}$, $V_{GS}=0\text{ to }-10\text{ V}$
Gate to drain charge	Q_{gd}	-	7.4	11.1	nC	$V_{DD}=-15\text{ V}$, $I_D=-20\text{ A}$, $V_{GS}=0\text{ to }-10\text{ V}$
Switching charge	Q_{sw}	-	18.4	25.7	nC	$V_{DD}=-15\text{ V}$, $I_D=-20\text{ A}$, $V_{GS}=0\text{ to }-10\text{ V}$
Gate charge total	Q_g	-	43.2	57.5	nC	$V_{DD}=-15\text{ V}$, $I_D=-20\text{ A}$, $V_{GS}=0\text{ to }-10\text{ V}$
Gate plateau voltage	$V_{plateau}$	-	-4.5	-	V	$V_{DD}=-15\text{ V}$, $I_D=-20\text{ A}$, $V_{GS}=0\text{ to }-10\text{ V}$
Output charge	Q_{oss}	-	34.9	46.4	nC	$V_{DD}=-15\text{ V}$, $V_{GS}=0\text{ V}$

¹⁾ See Fig. 3 for more detailed information

Table 7 Reverse diode

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Diode continuous forward current	I_S	-	-	-40	A	$T_C=25\text{ °C}$
Diode pulse current	$I_{S,pulse}$	-	-	-160	A	$T_C=25\text{ °C}$
Diode forward voltage	V_{SD}	-	-	-1.1	V	$V_{GS}=0\text{ V}$, $I_F=-40\text{ A}$, $T_j=25\text{ °C}$
Reverse recovery time	t_{rr}	-	39	-	ns	$V_R=15\text{ V}$, $I_F= I_S $, $di_F/dt=100\text{ A}/\mu\text{s}$
Reverse recovery charge	Q_{rr}	-	34	-	nC	$V_R=15\text{ V}$, $I_F= I_S $, $di_F/dt=100\text{ A}/\mu\text{s}$

4 Electrical characteristics diagrams







Diagram 5: Typ. output characteristics




$I_D = f(V_{DS})$; $T_j = 25^\circ\text{C}$; parameter: V_{GS}

Diagram 6: Typ. drain-source on resistance




$R_{DS(on)} = f(I_D)$; $T_j = 25^\circ\text{C}$; parameter: V_{GS}

Diagram 7: Typ. transfer characteristics




$I_D = f(V_{GS})$; $|V_{DS}| > 2|I_D|R_{DS(on)max}$; parameter: T_j

Diagram 8: Typ. forward transconductance




$g_{fs} = f(I_D)$; $T_j = 25^\circ\text{C}$

Diagram 9: Drain-source on-state resistance




$R_{DS(on)} = f(T_j)$; $I_D = -20$ A; $V_{GS} = -10$ V

Diagram 10: Typ. gate threshold voltage




$V_{GS(th)} = f(T_j)$; $V_{GS} = V_{DS}$; $I_D = -105$ μ A

Diagram 11: Typ. capacitances




$C = f(V_{DS})$; $V_{GS} = 0$ V; $f = 1$ MHz

Diagram 12: Forward characteristics of reverse diode




$I_F = f(V_{SD})$; parameter: T_j

Diagram 13: Avalanche characteristics




$I_{AS}=f(t_{AV})$; $R_{GS}=25\ \Omega$; parameter: $T_{j(start)}$

Diagram 14: Typ. gate charge




$V_{GS}=f(Q_{gate})$; $I_D=-20\text{ A}$ pulsed; parameter: V_{DD}

Diagram 15: Drain-source breakdown voltage




$V_{BR(DSS)}=f(T_j)$; $I_D=-250\ \mu A$

Diagram Gate charge waveforms



5 Package Outlines



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	0.90	1.10	0.035	0.043
b	0.24	0.44	0.009	0.017
b1	0.10	0.30	0.004	0.012
b2	0.20	0.44	0.008	0.017
D=D1	3.20	3.40	0.126	0.134
D2	2.15	2.45	0.085	0.096
E	3.20	3.40	0.126	0.134
E4	1.60	1.81	0.063	0.071
E5	0.59	0.86	0.023	0.034
e	0.65		0.026	
N	8		8	
L	0.30	0.56	0.012	0.022
L1	0.33	0.60	0.013	0.024
aaa	0.25		0.010	
F1	3.80		0.150	
F2	2.29		0.090	
F3	0.31		0.012	
F4	0.34		0.013	
F5	0.65		0.026	
F6	0.80		0.031	
F7	2.36		0.093	




Figure 1 Outline PG-TSDSON-8, dimensions in mm/inches

Revision History

BSZ086P03NS3 G

Revision: 2019-12-03, Rev. 2.4

Previous Revision

Revision	Date	Subjects (major changes since last revision)
2.4	2019-12-03	Update SOA Diagram

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:

erratum@infineon.com

Published by

Infineon Technologies AG

81726 München, Germany

© 2019 Infineon Technologies AG

All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[BSZ086P03NS3GXT](#)