






HONEYWELL PART NUMBER
5EN47-6
FAA-PMA 

REV	DOCUMENT	CHANGED BY	CHECK
16	0006860	CVS 03AUG04	AK



- NOTES
- 1 - CORROSION RESISANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805, SYMBOL 4
 - 3 - CIRCUIT DIAGRAM AND CATALOG LISTING, DATE CODE, FED MFG CODE AND FAA-PMA ARE SHOWN ON NAMEPLATE
 - 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .015 INCH OF PLUNGER TRAVEL
 - 5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 6 - FOR MANUFACTURING DETAIL SEE ASSEMBLY DRAWING 5EN47-6 FOR FAA-PMA

CHARACTERISTICS		ELECTRICAL DATA	
OPERATING FORCE ----- 6-12 LB		CONTACT ARRANGEMENT	
FULL OVERTRAVEL FORCE ----- 30 LB MAX		4X S P D T	
RELEASE FORCE ----- 4 LB MIN		28 VDC	
PRETRAVEL ----- .040 MAX		LOAD	SEA LEVEL 50,000 FT
DIFFERENTIAL TRAVEL ----- .030 MAX		RES	4 4
OVERTRAVEL ----- .250 MIN		IND	2 2
		MOTOR	4
		LAMP	

DESIGN UNITS: INCH			DRAWN	GJW	26OCT00	Honeywell			
TOLERANCES UNLESS NOTED:			CHECK	SAV	26OCT00				
NO PLACE	X	±	0.04	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		TITLE			
ONE PLACE	.X	±	.030						
TWO PLACE	.XX	±	.015						
THREE PLACE	.XXX	±	.005						
FOUR PLACE	.XXXX	±	0.0001						
ANGLES	X	±	0	INTERPRET PER ANSI Y14.5M 1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		SIZE	TYPE	DRAWING NAME	REV
THIRD ANGLE PROJECTION						C	I	5EN47-6	16
				Pro/ENGINEER 2D		SCALE	FULL	WEIGHT: 14.4 OZ MAX	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[5EN47-6](#)