Honeywell

Commercial Thermostats



DESCRIPTION

Thermostats can provide either temperature control or overtemperature protection by breaking electrical contact when a specified temperature is reached.

Honeywell manufactures a wide range of 12,7 mm [0.5 in] commercial snap-action thermostats for possible use in a wide array of small and major appliances, office copy machines, medical equipment, heat detectors, HVAC equipment and more.

These snap-action thermostats include automatic and manual reset options, phenolic or ceramic housings and a wide variety of mounting brackets and terminal options.

Each thermostat's design is configured from a base unit, and may be customized for temperature tolerance and mechanical configurations, meeting the customer's needs for accuracy and exactitude.

Honeywell can also integrate these thermostats in higher value cable assemblies, incorporating wire harness and connectors.


TABLE OF CONTENTS

DESCRIPTION	р. 1
NOMENCLATURE	p. 2
DEFINITION OF TERMS	р. З
NOTES	р. З
COMMERCIAL THERMOSTATS	
2450R/2450HR/2455R/2452R/2452HR Series Phenolic Automatic Reset	p. 4
2450RC/2450RCH/2455RC Series Ceramic Automatic Reset	p. 6
2455RM/2450CM Series Phenolic or Ceramic Manual Reset	p. 9
2455RD Series Phenolic Manual Reset	p. 11
2455RBV Series Overmolded Automatic Reset	р. 13
2450A/2455RA Series Heat Detection	p. 15
2450R/2455R/2450RC/2455RC/2450HR/2450RCH Series "One Shot"	p. 17
REDI-TEMP THERMOSTATS	
3455RC Series	р. 19
MOUNTING HARDWARE	
Brackets	p. 20
Brass mounting studs	p. 21
Terminals	p. 22

NOMENCLATURE

The nomenclature given in Figure 1 is provided for reference only.

Figure 1. Commercial Thermostat Nomenclature



DEFINITION OF TERMS

- Automatic Reset: A type of thermostat that will automatically reset at a specific temperature (i.e. a thermostat operates at 65,5 °C [150 °F] and resets at 48,89 °C [120 °F]).
- **Bimetal:** Two dissimilar metals bonded together to form the material for manufacturing thermally-sensitive discs which actuate the thermostat.
- Close on Rise (COR): Refers to operation of the contacts. When the temperature rises to its set point, the contacts close or make contact and complete the circuit.
- Contact Resistance: The value of resistance measured between the terminals.
- **Dielectric Strength**: The value of insulation between two electrically conducting parts. It may be tested by the application of a predetermined overvoltage for a specified time.
- Differential: The temperature difference between the operate and reset set points, also known as operate and reset.
 - **Nominal:** The temperature difference between nominal set points regardless of tolerance.
 - Maximum: Maximum number of degrees between actual opening and closing set points.
 - Minimum: Minimum number of degrees between actual opening and closing set points.
- Exposure Temperature: Thermal environment of a device during application operation.
- FLA (Full Load Amps): Current taken from the line by the motor when the motor is yielding the rated hp at the rated voltage and frequency.
- Life Cycles: The endurance rating of the thermostat expressed in number of operations with stated electrical load applied. Temperature limit application = open on rise.
- LRA (Locked Rotor Amps): The amount of current the motor can be expected to draw under starting conditions when full voltage is applied, also known as starting inrush current.
- Manual Reset: A bimetal thermostat with a reset button that must be pressed to reset the contacts.
- **Open on Rise (OOR):** Refers to the operation of contacts. When the temperature rises to its set point the contacts open, terminating the circuit.
- **Overmold:** Encapsulation with an insulating material.
- Phenolic: Thermoset plastic used for the insulating body of the thermostat.
- Set Point: The nominal temperature at which the thermostat operates.
- SPST (Single Pole/Single Throw): A switch with one current path which can be either open or closed.
- **Tolerance:** The allowable range above and below the set point temperature.
- Operate: Change of state when the thermostat reaches its set point.
- Reset: Change of state when the thermostat returns to its original condition prior to operation.

NOTES

• Standard Temperature Characteristics Tables:

- Temperatures: Please consult applications engineering for temperature ranges, tolerances and differentials not noted.
 The operating temperature ranges include tolerances.
- **Tolerances:** The ± tolerances given have been established after review of many thermostat applications. Attempts should be made to establish the widest acceptable tolerance possible.
- UL and CSA Approvals: 12,7 mm [0.5 in] thermostats are available with multiple agency approval for incorporation into equipment.
- Fan control applications: Require thermostat set points to be derated by 20 °C from the equivalent temperature limit application. They also close on rise.
- Dimensions: Are for reference only and are given in mm [in].

Figure 2. 2450R/2450HR/2455R/2452R/2452HR Series Phenolic Automatic Reset Thermostat



The 2450R/2450HR/2455R/2452R/2452HR Series is a single pole, single throw, snap-acting, non-adjustable thermostat which may be used in applications such as power supplies, general appliances and medical equipment. A temperature-sensitive bimetal disc, electrically and thermally isolated from the switch, is used to actuate the normally-closed contacts. Contacts open when surface or ambient temperatures increase to the operating set point of the calibrated bimetal disc. The entire switch is enclosed in a phenolic housing; the bimetal disc is retained by a metal heat-conducting end cap. Due to the small size of this unit and the inherently low mass of the bimetal snap-action disc, response of this thermostat to temperature changes is extremely rapid, compared to other commercially available thermostatic devices. A variety of mounting brackets and terminals are available.

All versions are UL/CSA approved. The 2452R/2452HR/2455R version meets the requirements of EN60730-01.

Potential applications include:

- Power supplies
- Appliances
- Medical equipment
- Water heaters
- Office automation
- Industrial equipment
- HVAC equipment

Table 1. 2450R/2450HR/2455R/2452R/2452HR Series Standard Temperature Characteristics

Operating Temperature Range	Tole	erance	Standard Mean Differential
	Open	Close	°C [°F]
	°C [°F]	°C [°F]	
	±4 [±7]	±6 [±10]	28 to 34 [50 to 60]
0 °C to 26 °C	±4 [±6]	±6 [±10]	22 to 27 [40 to 49]
[32 °F to 79 °F]	±4 [±6]	±5 [±9]	17 to 22 [30 to 39]
	±4 [±6]	±5 [±8]	14 to 16 [25 to 29]
	±3 [±5]	±5 [±8]	8 to 14 [15 to 24]
	±5 [±9]	±8 [±15]	45 to 56 [81 to 100]
	±4 [±7]	±6 [±11]	34 to 45 [61 to 80]
27 °C to 82 °C	±4 [±6]	±6 [±10]	28 to 34 [50 to 60]
[80 °F to 180 °F]	±3 [±5]	±6 [±10]	22 to 27 [40 to 49]
	±3 [±5]	±5 [±9]	17 to 22 [30 to 39]
	±3 [±5]	±5 [±8]	8 to 16 [15 to 29]
	±6 [±10]	±8 [±15]	45 to 56 [81 to 100]
	±5 [±8]	±8 [±15]	34 to 45 [61 to 80]
83 °C to 110 °C	±4 [±7]	±7 [±12]	28 to 34 [50 to 60]
[181 °F to 230 °F]	±4 [±6]	±6 [±10]	22 to 27 [40 to 49]
	±4 [±6]	±5 [±9]	17 to 22 [30 to 39]
	±4 [±6]	±5 [±8]	8 to 16 [15 to 29]
	±7 [±12]	±10 [±18]	45 to 56 [80 to 100]
	±5 [±9]	±8 [±15]	34 to 45 [61 to 80]
111 °C to 150 °C	±5 [±8]	±7 [±12]	28 to 34 [50 to 60]
[231 °F to 302 °F]	±4 [±7]	±7 [±12]	22 to 27 [40 to 49]
	±4 [±7]	±6 [±11]	17 to 22 [30 to 39]
	±4 [±7]	±6 [±10]	14 to 16 [25 to 29]

Characteristic	Parameter	
Switch type	SPST	
Reset type	automatic	
Amperage	See Tables 3, 4	
Voltage	120 Vac to 250 Vac	
Operating temperature range	0 °C to 150 °C [32 °F to 302 °F]	
Environmental exposure range	-18 °C to 177 °C [0 °F to 350 °F]	
Materials:		
Base	phenolic	
Contacts	silver alloy	
Terminals	unplated brass, plated brass or steel	
Closure	aluminum, brass or stainless steel	
Brackets	aluminum or stainless steel	
UL and CSA approvals	• 2455R: 6,35 mm [0.25 in] clearance; UL File MH8267, UL File E36103; CSA File LR21048	
	 2450HR: 1,59 mm [0.0625 in] clearance; UL File E36103; CSA File LR21048 	
	 2450R: 1,59 mm [0.0625 in] clearance; UL File E36103; CSA File LR 21048 	
 2452R: 2.66mm [0.105 in] clearance; UL E36103 		
	 2452HR: 2.66mm [0.105 in] clearance; UL36103 	
Weight	6 g [0.2 oz] (does not include brackets or wire leads)	

Table 2. 2450R/2450HR/2455R/2452R/2452HR Series Specifications

Table 3. 2450R/2450HR/2452R/2452HR Contact Ratings

Life Cycles	120 Vac	240 Vac	277 Vac
100,000	15 A resistive	10 A resistive	10 A resistive
30,000	125 VA pilot duty	125 VA pilot duty	-

Note: 2450 approval rating is limited by EN60730-1 to 125 Vac max.

Table 4. 2455R Contact Ratings

Life Cycles	120 Vac	240 Vac	277 Vac
100,000	15 A resistive	10 A resistive	7.2 A resistive
	4.4 FLA 26.4 LRA	2.2 FLA 13.2 LRA	
	125 VA pilot duty	125 VA pilot duty	
6,000	5.8 FLA, 34.8 LRA	2.9 FLA, 17.4 LRA	-

Note: Additional contact ratings are available, please contact Honeywell.

Figure 3. 2450R/2450HR/2455R/2452R/2452HR Basic Dimensions




Figure 4. 2450RC/2450RCH/2455RC Series Automatic Reset Thermostat



Table 5. 2450RC/2450RCH/2455RC Series Standard Temperature Characteristics

Operating Temperature Range	Tole	rance	Standard Mean Differential
	Open	Close	°C [°F]
	°C [°F]	°C [°F]	
	±4 [±7]	±6 [±10]	28 to 34 [50 to 60]
0 °C to 26 °C	±4 [±6]	±6 [±10]	22 to 27 [40 to 49]
[32 °F to 79 °F]	±4 [±6]	±5 [±9]	17 to 22 [30 to 39]
	±4 [±6]	±5 [±8]	14 to 16 [25 to 29]
	±3 [±5]	±5 [±8]	8 to 14 [15 to 24]
	±5 [±9]	±8 [±15]	45 to 56 [81 to 100]
	±4 [±7]	±6 [±11]	34 to 45 [61 to 80]
27 °C to 82 °C	±4 [±6]	±6 [±10]	28 to 34 [50 to 60]
[80 °F to 180 °F]	±3 [±5]	±6 [±10]	22 to 27 [40 to 49]
	±3 [±5]	±5 [±9]	17 to 22 [30 to 39]
	±3 [±5]	±5 [±8]	8 to 16 [15 to 29]
	±6 [±10]	±8 [±15]	45 to 56 [81 to 100]
	±5 [±8]	±8 [±15]	35 to 45 [61 to 80]
83 °C to 110 °C	±4 [±7]	±7 [±12]	28 to 34 [50 to 60]
[181 °F to 230 °F]	±4 [±6]	±6 [±10]	22 to 27 [40 to 49]
	±4 [±6]	±5 [±9]	17 to 22 [30 to 39]
	±4 [±6]	±5 [±8]	8 to 16 [15 to 29]

Operating Temperature Range	Tole	erance	Standard Mean Differential
	Open	Close	°C [°F]
	°C [°F]	°C [°F]	
	±7 [±12]	±10 [±18]	45 to 56 [81 to 100]
	±5 [±9]	±8 [±15]	34 to 45 [61 to 80]
111 °C to 149 °C	±5 [±8]	±7 [±12]	28 to 34 [50 to 60]
[231 °F to 300 °F]	±4 [±7]	±7 [±12]	22 to 27 [40 to 49]
	±4 [±7]	±6 [±11]	17 to 22 [30 to 39]
	±4 [±7]	±6 [±10]	14 to 16 [25 to 29]
	±8 [±15]	±11 [±20]	39 to 45 [71 to 80]
150 °C to 170 °C	±6 [±10]	±11 [±20]	34 to 39 [61 to 70]
[301 °F to 335 °F]	±6 [±10]	±8 [±15]	28 to 33 [50 to 60]
	±6 [±10]	±7 [±12]	22 to 27 [40 to 49]
171 °C to 200 °C	±14 [±25]	±14 [±25]	51 to 56 [91 to 100]
171 °C to 220 °C	±11 [±20]	±11 [±20]	39 to 50 [71 to 90]
	±8 [±15]	±11 [±20]	28 to 39 [50 to 70]
001 °C to 005 °C	±14 [±25]	±14 [±25]	51 to 56 [91 to 100]
221 °C to 235 °C	±11 [±20]	±11 [±20]	39 to 50 [71 to 90]
[426 °F to 450 °F]	±8 [±15]	±11 [±20]	28 to 39 [50 to 70]
236 °C to 260 °C	±14 [±25]	±14 [±25]	31 to 56 [60 to 100]
[451 °F to 500 °F]	±11 [±20]	±11 [±20]	28 to 50 [50 to 90]

Table 6. 2450RC/2450RCH/2455RC Series Standard Temperature Characteristics (continued)

Table 7. 2450RC/2450RCH/2455RC Series Specifications

Characteristic	Parameter	
Switch type	SPST	
Reset type	automatic	
Amperage	See Tables 8, 9	
Voltage	120 Vac to 250 Vac	
Operating temperature range	0 °C to 260 °C [32 °F to 500 °F]	
Environmental exposure range	-20 °C to 287 °C [0 °F to 550 °F]	
Materials:		
Base	ceramic	
Contacts	silver alloy	
Terminals	plated steel	
Closure	aluminum, brass, or stainless steel	
Brackets	stainless steel	
Approvals	 2450RCH: 1,59 mm [0.0625 in] clearance through air and over surface; UL File E36103; CSA File LR21048 	
	• 2450RC: 1,59 mm [0.0625 in] clearance; UL file E36103; CSA File LR21048	
	• 2455RC: 6,35 mm [0.25 in] clearance; UL File E36103; CSA File LR21048	
Weight	6 g [0.21 oz] (does not include brackets or wire leads)	

Table 8. 2450RCH/2450RC Contact Ratings


Life Cycles	120 Vac	240 Vac
100,000	15 A resistive	10 A resistive
30,000	125 VA pilot duty	125 VA pilot duty

Table 9. 2455RC Contact Ratings

Life Cycles	120 Vac	240 Vac
100,000	15 A resistive	10 A resistive
100,000	4.4 FLA 26.4 LRA	2.2 FLA 13.2 LRA
100,000	125 VA pilot duty	125 VA pilot duty

Note: Additional contact ratings are available, please contact Honeywell.

Figure 5. 2450RC/2450RCH/2455RC Basic Dimensions



The 2455RM (phenolic)/2450CM (ceramic) Series is a All versions are UL/CSA, European approved. single pole, single throw, snap-acting, non-adjustable thermostat. A temperature-sensitive bimetal disc, electrically Potential applications include those where a manual reset is and thermally isolated from the switch, is used to actuate desired, including: the normally-closed contacts. Contacts open when surface or ambient temperatures increase to the operating set point Power supplies ٠ of the calibrated bimetal disc. The entire switch is enclosed ٠ Appliances in a housing; the bimetal disc is retained by a metal heat-conducting end cap. The circuit remains open above the Medical equipment ٠ Water heaters room ambient temperature until the manual reset button is • depressed. Due to the small size of this unit and the Office automation • inherently low mass of the bimetal snap-action disc, Industrial equipment • response of this thermostat to temperature changes is HVAC equipment extremely rapid, compared to other commercially available thermostatic devices. For increased sensitivity, an exposed bimetal disc may be specified. A variety of mounting brackets and terminals is available.

Figure 6. 2455RM/2450CM Series Phenolic or Ceramic Manual Reset Thermostats

Table 10. 2455RM Series Standard Temperature Characteristics

Operating Temperature Range	Tolerance °C [°F]
52 °C to 93 °C [125 °F to 200 °F]	±5 [±8]
94 °C to 121 °C [201 °F to 250 °F]	±6 [±10]
122 °C to 150 °C [251 °F to 302 °F]	±7 [±12]

Table 11. 2450CM Series Standard Temperature Characteristics

Operating Temperature Range	Tolerance °C [°F]
52 °C to 93 °C [125 °F to 200 °F]	±5 [±8]
94 °C to 121 °C [201 °F to 250 °F]	±6 [±10]
122 °C to 149 °C [251 °F to 300 °F]	±7 [±12]
150 °C to 177 °C [301 °F to 350 °F]	±8 [±15]
177 °C to 204 °C [351 °F to 400 °F]	±10 [±18]
205 °C to 232 °C [401 °F to 450 °F]	±11 [±20]

Characteristic	Parameter	
Switch type	SPST	
Reset type	manual	
Amperage	15 A resistive at 6,000 cycles (UL); 16 A resistive at 1000 cycles (EU)	
Voltage	120 Vac to 250 Vac	
Operating temperature range	2455RM: 52 °C to 150 °C [125 °F to 302 °F]	
	2450CM: 52 °C to 232 °C [125 °F to 450 °F]	
Environmental exposure range	2455RM: -20 °C to 177 °C [0 °F to 350 °F]	
	2450CM: -20 °C to 260 °C [0 °F to 500 °F]	
Materials:		
Base	2455RM: phenolic; 2450CM: ceramic	
Contacts	silver alloy	
Terminals	2455RM: unplated brass, plated brass or steel; 2450CM: plated steel	
Closure	aluminum, brass, or stainless steel	
Brackets	stainless steel	
Approvals	UL File E36103, CSA File LR21048	
Weight	6 g [0.21 oz] (does not include brackets or wire leads)	

Table 12. 2455RM/2450CM Series Specifications

NOTICE

 2455RM/2450CM thermostats are intended as a manual reset control. They are not to be used on applications where a limit thermostat is required unless back-up protection is provided. Units have been tested by UL for 1,000 cycles under load, 5,000 cycles no load, and are not considered as limit devices.

- This range of thermostats has an automatic reset function with manual override function.
- Reset pin operation should not be performed above 70% of set point temperature.

Table 13. 2450CM/2455RM Contact Ratings

Life Cycles	120 Vac	240 Vac
6,000	15 A resistive	10 A resistive
6,000	4.4 FLA 26.4 LRA	2.2 FLA 13.2 LRA
	125 VA pilot duty	125 VA pilot duty

Note: Additional contact ratings are available, please consult Honeywell.

Figure 7. 2455RM/2455CM Basic Dimensions




Figure 8. 2455RD Series Phenolic Manual Reset



The 2455RD Series is a single pole, single throw, snapacting, non-adjustable thermostat. A temperature-sensitive bimetal disc, electrically and thermally isolated from the switch, is used to actuate the normally-closed contacts. Contacts open when surface or ambient temperatures increase to the operating set point of the calibrated bimetal disc. The entire switch is enclosed in a housing; the bimetal disc is retained by a metal heat-conducting end cap. The circuit remains open above the room ambient temperature until the manual reset button is depressed. (These devices are constructed with an additional steel disc so that they are manual reset only. They do not have an automatic reset.) Due to the small size of this unit and the inherently low mass of the bimetal snap-action disc, response of this thermostat to temperature changes is extremely rapid, compared to other commercially available thermostatic devices. For increased sensitivity, an exposed bimetal disc may be specified. A variety of mounting brackets and terminals is available.

All versions are UL/CSA and European approved.

Potential applications include those where a manual reset is desired, including:

- Power supplies
- Appliances
- Medical equipment
- Water heaters
- Office automation
- Industrial equipment
- HVAC equipment

Table 14. 2455RD Series Standard Temperature Characteristics

Operating Temperature Range	Tolerance °C [°F]
52 °C to 93 °C [125 °F to 200 °F]	±5 [±8]
94 °C to 121 °C [201 °F to 250 °F]	±6 [±10]
122 °C to 150 °C [251 °F to 302 °F]	±7 [±12]

Table 15. 2455RD Series Specifications


Characteristic	Parameter
Switch type	SPST
Reset type	manual
Amperage	15 A resistive at 6,000 cycles (UL); 16 A resistive at 1000 cycles (EU)
Voltage	120 Vac to 250 Vac
Operating temperature range	2455RD: 52 °C to 150 °C [125 °F to 302 °F]
Environmental exposure range	2455RD: -20 °C to 177 °C [0 °F to 350 °F]
Materials:	
Base	phenolic
Contacts	silver alloy
Terminals	unplated brass, plated brass or steel
Closure	aluminum, brass, or stainless steel
Brackets	stainless steel
Approvals	UL File E36103, CSA File LR21048

Table 16. 2455RD Contact Ratings

Life Cycles	120 Vac	240 Vac
6000	15 A resistive	10 A resistive

Note: Additional contact ratings are available, please consult Honeywell.

Figure 9. 2455RD Basic Dimensions



C Reset button

Figure 10. Series 2455RBV Overmolded Automatic Reset Thermostats




Table 17. 2455RBV Series Standard Temperature Characteristics

Operating Temperature Range	Tole	rance	Standard Mean Differential
	Open °C [°F]	Close °C [°F]	°C [°F]
10.0 °C to 06.7 °C	±4 [±7]	±6 [±10]	17 to 44 [30 to 80]
-12,2 °C to 26,7 °C	±3 [±6]	±4 [±8]	14 to 28 [25 to 50]
	±3 [±5]	±4 [±8]	11 to 22 [20 to 40]
27,2 °C to 105 °C	±3 [±6]	±6 [±10]	17 to 44 [30 to 80]
[81 °F to 221 °F]	±3 [±5]	±4 [±8]	11 to 28 [20 to 50]

Characteristic	Parameter	
Switch type	SPST	
Reset type	automatic	
Amperage	see Table 19	
Voltage	120 Vac to 250 Vac	
Operating temperature range	0 °C to 105 °C [32 °F to 221 °F]	
Environmental exposure range	-18 °C to 126.6 °C [0 °F to 260 °F]	
Materials:		
Boot	nylon, with epoxy filled or injection molded	
Base	internal 2455RC ceramic or 2455R phenolic	
Contacts	silver alloy	
Terminals	plated steel with wires	
Closure	aluminum, brass, or stainless steel	
Brackets	stainless steel	
Approvals	UL File SA4469, CSA File LR21048.	
Weight	6.5 g [0.23 oz] (does not include brackets or wire leads)	

Table 19. 2455RBV Series Contact Ratings

Life Cycles	120 Vac	240 Vac
100,000	15 A resistive	10 A resistive
6,000	5.8 FLA 34.8 LRA	2.9 FLA 17.4 LRA
100,000	4.4 FLA 26.4 LRA 2.2 FLA 13.2 LRA	
	125 VA pilot duty	125 VA pilot duty

Note: Additional contact ratings are available, please contact Honeywell.

Figure 11. 2455RBV Basic Dimensions




Figure 12. 2450A/2455RA Heat Detection Thermostats



NOTICE

Final approval of a fire detection system is determined by UL as outlined in UL #521 and UL #217 for the suitability of the combination of the thermostat (2450A/2455RA) and the user's mounting base, together with its intended application of the total fire detection system. To assist the use with design and testing , a minimum of 0.25 in extension beyond the housing is recommended.

Table 20. 2450A/2455RA Series Standard Temperature Characteristics

Detection (0	Close on Rise)	Release (Op	oen on Rise)
Close °C [°F]	Open °C [°F]	Open °C [°F]	Close °C [°F]
47 ±3 [117±5]	30 min [85 min]	57 ±3 [117 ±5]	30 min [85 min]
57 ±3 [135 ±5]	32 min [90 min]	57 ±3 [135 ±5]	32 min [90 min]
69 ±3 [156 ±5]	32 min [90 min]	69 ±3 [156 ±5]	32 min [90 min]
85 ±4 [185 ±7]	32 min [90 min]	85 ±4 [185 ±7]	32 min [90 min]
107 ±4 [225 ±7]	32 min [90 min]	107 ±4 [225 ±7}	32 min [90 min]

Notes:


Additional switches can be provided as long as they fall between 47,2 °C to 107,2 °C [117 °F to 225 °F] close on rise or open or rise.

• Please consult Honeywell for tolerances and temperatures not listed.

Characteristic	Parameter
Switch type	SPST
Reset type	automatic
Amperage	3 A
Voltage	120 Vac
Operating temperature range	47,2 °C to 107,2 °C [117 °F to 225 °F]
Environmental exposure range	-0 °C to 150 °C [32 °F to 302 °F]
Materials:	
Base	phenolic
Contacts	gold flash
Terminals	unplated brass, plated brass
Closure	aluminum
Brackets	aluminum
Approvals	UL File S1015 and S1389; Guide USCV2 and TAOZ2, UL Standard #521, #217
Weight	6 g [0.21 oz] (does not include brackets)

Table 21. 2450A/2455RA Series Specifications

Figure 13. 2450A/2455RA Basic Dimensions








Figure 16. 2450R/2455R/2450RC/2455RC/2450HR/2450RCH Series "One Shot" Thermostats

Table 22. 2450R/2455R/2450RC/2455RC/2450HR/2450RCH Series "One Shot" Standard Temperature Characteristics

Operating Temperature Range	Tolerance °C [°F]
52 °C to 93 °C [125 °F to 200 °F]	5 [8]
94 °C to 121 °C [201 °F to 250°F]	6 [10]
122 °C to 149 °C [251 °F to 300 °F]	7 [12]
150 °C to 177 °C [301 °F to 350 °F]	8 [15]
177 °C to 204 °C [351 °F to 400 °F]	10 [18]
205 °C to 232 °C [401 °F to 450 °F]	11 [20]
232 °C to 260 °C [451 °F to 500 °F]	14 [25]

Characteristic	Parameter
Switch type	SPST
Reset type	One Shot
Amperage	see Table 24
Voltage	120 Vac to 250 Vac
Operating temperature range	2450R/2455R/2450HR/2450RCH: 52 °C to 150 °C [125 °F to 302 °F]
	2450RC/2455RC: 52 °C to 260 °C [125 °F to 500 °F]
Environmental exposure range	2450R/2455R/2450HR/2450RCH: 17.8 °C to 177 °C [0 °F to 350 °F]
	2450RC/2455RC: 17.8 °C to 287 °C [125 °F to 550 °F]
Materials:	
Base	phenolic or ceramic
Contacts	silver alloy
Terminals	unplated brass, plated brass or steel
Closure	aluminum, brass, stainless steel
Brackets	stainless steel
Approvals	UL File E36103, CSA File LR43279
Weight	6 g [0.21 oz] (does not include brackets or lead wires)

Table 23. 2450R/2455R/2450RC/2455RC/2450HR/2450RCH Series "One Shot" Specifications


Table 24. 2450R/2455R/2450RC/2455RC/2450HR/2450RCH Series "One Shot" Contact Ratings

Cycles	120 Vac	240 Vac	277 Vac
1	15 A resistive	10 A resistive	10 A resistive

Notes:

- Resets below -35 °C [-31 °F].
- Additional contact ratings are available. Please consult Honeywell.

Figure 17. 2450R/2455R/2450RC/2455RC/2450HR/2450RCH Series "One Shot" Basic Dimension



REDI-TEMP THERMOSTATS

REDI-TEMP thermostats are pre-configured as shown and are readily available.

Figure 18. 3455RC REDI-TEMP Series (See page 6 for specifications and potential applications.)






Table 25. 3455RC REDI-TEMP Series Open on Rise

Catalog Listing	Open Temp. °C [°F]	Open Tolerance °C [°F]	Close Temp. °C [°F]	Close Tolerance °C [°F]
3455RC-100-220	18 [65]	±3 [±5]	-1 [30]	±5 [±8]
3455RC-100-221	24 [75]	±3 [±5]	4 [40]	±5 [±8]
3455RC-100-222	29 [85]	±3 [±5]	13 [55]	±5 [±8]
3455RC-100-223	35 [95]	±3 [±5]	18 [65]	±5 [±8]
3455RC-100-224	41 [105]	±3 [±5]	24 [75]	±5 [±8]
3455RC-100-225	46 [115]	±3 [±5]	29 [85]	±5 [±8]
3455RC-100-226	52 [125]	±3 [±5]	35 [95]	±5 [±8]
3455RC-100-227	57 [135]	±3 [±5]	41 [105]	±5 [±8]
3455RC-100-228	63 [145]	±3 [±5]	46 [115]	±5 [±8]
3455RC-100-229	68 [155]	±3 [±5]	52 [125]	±5 [±8]
3455RC-100-230	73 [165]	±3 [±5]	57 [135]	±5 [±8]
3455RC-100-231	79 [175]	±3 [±5]	63 [145]	±5 [±8]
3455RC-100-232	85 [185]	±3 [±5]	68 [155]	±5 [±8]
3455RC-100-233	91 [195]	±3 [±5]	73 [165]	±5 [±8]
3455RC-100-234	96 [205]	±4 [±6]	79 [175]	±5 [±8]
3455RC-100-235	102 [215]	±4 [±6]	85 [185]	±5 [±8]
3455RC-100-236	107 [225]	±4 [±6]	91 [195]	±5 [±8]
3455RC-100-237	113 [235]	±4 [±6]	96 [205]	±5 [±8]
3455RC-100-238	118 [245]	±4 [±6]	102 [215]	±5 [±8]
3455RC-100-239	124 [255]	±4 [±7]	107 [225]	±5 [±8]
3455RC-100-240	135 [275]	±4 [±7]	118 [245]	±5 [±8]
3455RC-100-241	146 [295]	±4 [±7]	129 [265]	±5 [±8]
3455RC-100-242	157 [315]	±6 [±10]	135 [275]	±8 [±15]

Table 26. 3455RC REDI-TEMP Series Close on Rise

Catalog Listing	Close Temp. °C [°F]	Close Tolerance °C [°F]	Open Temp. °C [°F]	Open Tolerance °C [°F]
3455RC-100-243	21 [70]	±5 [±8]	2 [35]	±3 [±5]
3455RC-100-244	32 [90]	±5 [±8]	16 [60]	±3 [±5]
3455RC-100-245	43 [110]	±5 [±8]	27 [80]	±3 [±5]
3455RC-100-246	54 [130]	±5 [±8]	38 [100]	±3 [±5]
3455RC-100-247	66 [150]	±5 [±8]	49 [120]	±3 [±5]
3455RC-100-248	77 [170]	±5 [±8]	60 [140]	±3 [±5]
3455RC-100-249	88 [190]	±5 [±8]	71 [160]	±3 [±5]
3455RC-100-250	99 [210]	±5 [±8]	82 [180]	±4 [±6]
3455RC-100-251	110 [230]	±5 [±8]	93 [200]	±4 [±6]

Note: Materials and contact ratings are the same as those for 2455RC.

MOUNTING HARDWARE




Figure 19. Brackets (Continued)






Figure 20. Brass Mounting Studs








Figure 21. Terminals (Continued)

A WARNING

PERSONAL INJURY

DO NOT USE these products as safety or emergency stop devices or in any other application where failure of the product could result in personal injury.

Failure to comply with these instructions could result in death or serious injury.

WARRANTY/REMEDY

Honeywell warrants goods of its manufacture as being free of defective materials and faulty workmanship. Honeywell's standard product warranty applies unless agreed to otherwise by Honeywell in writing; please refer to your order acknowledgement or consult your local sales office for specific warranty details. If warranted goods are returned to Honeywell during the period of coverage, Honeywell will repair or replace, at its option, without charge those items it finds defective. The foregoing is buyer's sole remedy and is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose. In no event shall Honeywell be liable for consequential, special, or indirect damages.

While we provide application assistance personally, through our literature and the Honeywell web site, it is up to the customer to determine the suitability of the product in the application.

Specifications may change without notice. The information we supply is believed to be accurate and reliable as of this printing. However, we assume no responsibility for its use.

A WARNING

MISUSE OF DOCUMENTATION

- The information presented in this product sheet is for reference only. Do not use this document as a product installation guide.
- Complete installation, operation, and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

SALES AND SERVICE

Honeywell serves its customers through a worldwide network of sales offices, representatives and distributors. For application assistance, current specifications, pricing or name of the nearest Authorized Distributor, contact your local sales office or:

E-mail: info.sc@honeywell.com

Internet: www.honeywell.com/sensing

Phone and Fax:

Asia Pacific	+65 6355-2828
	+65 6445-3033 Fax
Europe	+44 (0) 1698 481481
	+44 (0) 1698 481676 Fax
Latin America	a +1-305-805-8188
	+1-305-883-8257 Fax
USA/Canada	+1-800-537-6945
	+1-815-235-6847
	+1-815-235-6545 Fax

Sensing and Control Honeywell 1985 Douglas Drive North Golden Valley, MN 55422 www.honeywell.com

Honeywell

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

3450RG 80040512 2450A 02950006 2450A 02950007 2450A 02950008 2450A 05690001 2450A 80440041 2455RA 01060033 2455RA 01060034 2455RA 05280007 2455RA 05380003 2450R 00980175 2450R 80020544 2450R 80040406 2450R 80750289 2450R 80821021 2450R 81360026 2450R 81740203 2450R 83760023 2450R 84680004 2450HR 80030285 2450HR 80040479 2450HR 80920063 2450HR 81460048 2455R 00010444 2455R 00980166 2455R 01570038 2455R 01580037 2455R 05020001 2455R 80821016 2455R 81000452 2455R 82090072 2455R 82800055 2455R 87530002 2450RC 00040250 2450RC 00820401 2450RC 80430254 2450RC 81890031 2450RC 82000049 2450RC 82150051 2450RC 82330014 2450RC 85990004 2455RC 01740113 2455RC 02140006 2455RC 02180018 2455RC 80580153 2455RC 80750269 2455RC 80821003 2455RC 81740207 2455RC 82540068 2455RC 84370028 2455RC 86610001 2450RG 06180004 2450RG 80820923 2450RG 82040035 2450RG 85770007 2450RG 85890011 2450RG 86930002 2455RG 01240024 2455RG 80020479 2455RG 80820970 2455RG 81000480 2455RG 81570191 2455RM 80580181 2455RM 80750327 2455RM 80820998 2455RM 80980261 2455RM 81290040 2455RM 81740201 2455RM 82540070 2455RM 85010006 2455RM 86040003 2455RM 86230002 2450CM 80820818 2450CM 80880374 2450CM 80980269 2450CM 81000461 2450CM 81580060 2450CM 82140044 2450CM 82540067 2450CM 84210015 2450CM 86210191 2450CM 86750003 3450R 01000340 3450R 02150038 3450R 80430253 3450R 80820990 3450R 80840058 3450R 81290052 3450R 81550022 3450R 82700022 3450R 85170014 3450R 87540001 3450HR 04550008 3450HR 04550013 3450HR 84550019 3455R 00430212 3455R 00810062 3455R 01610050 3455R 02540040 3455R 04210010