

26PC --- 6D

CATALOG LISTING	LASER BRAND /8\
26PCAFA6D	6AF6D
26PCDFA6D	6DF6D
26PCFFA6D	6FF6D
26PCCFJ6D	6CF6D
26PCBFA6D	6BF6D
26PCCFA6D	6CF6D
26PCFNH6D	6FN6D
26PCFFT6D	6FF6D
26PCGFA6D	6GF6D
26PCGNH6D	6GN6D
26PCBVA6D	6BV6D
26PCCVA6D	6CV6D


- STYLE
(D) DIFFERENTIAL
TERMINATION
(6) 1 X 4 (.60 IN.)
PORT
(A) STRAIGHT
(H) 5mm THREAD
(J) SMALL NEEDLE
(T) LONG BARBED
SEAL
(F) FLUOROSILICONE
(N) NEOPRENE (70 DURO)
(V) VITON
PRESSURE
(A) 1 PSI
(B) 5 PSI
(C) 15 PSI
(D) 30 PSI
(E) 100 PSI
(F) 300 PSI
(G) 250 PSI

METRIC	INCHES
0.41	.016
0.51	.020
1.02	.040
1.3	.05
1.8	.07
1.93	.076
1.98	.078
2.0	.08
2.3	.09
2.5	.10
3.18	.125
4.06	.160
4.70	.185
5.1	.20
6.4	.25
7.9	.31
9.1	.36
11.2	.44
11.7	.46
12.7	.50
15.3	.60
16.5	.64
17.3	.68
19.1	.75
21.8	.86
22.1	.87
34.3	1.35
35.6	1.40
35.8	1.41
40.6	1.60

GENERAL OPERATING CHARACTERISTICS (ELECTRICAL PERFORMANCE AT 10.00 ±0.01 VDC EXCITATION, 25 °C)																				
PRESSURE RANGE (PSI)		0 - 1			0 - 5			0 - 15			0 - 30			0 - 100			0-250			
		MIN	NOM	MAX	MIN	NOM	MAX	MIN	NOM	MAX	MIN	NOM	MAX	MIN	NOM	MAX	MIN	NOM	MAX	UNITS
SPAN (P2>P1) /1\		14.7	16.7	18.7	47	50	53	97	100	103	95	100	103	95	100	105	143	150	157	mV
NULL OFFSET		-1.5	0	+1.5	-1.5	0	+1.5	-1.5	0	+1.5	-1.5	0	+1.5	-1.5	0	+2.0	-2.0	0	+2.0	mV
			TYP	MAX		TYP	MAX		TYP	MAX		TYP	MAX		TYP	MAX		TYP	MAX	UNITS
LINEARITY (BFSL, P2>P1)			0.25	0.5		0.4	0.5		0.25	0.5		0.1	0.2		0.4	0.6		0.5	0.7	%SPAN
NULL SHIFT (0 TO 25 °C, 25 TO 50 °C) /2\			±0.5	±1.0		±0.5	±1.0		±0.5	±1.0		±0.75	±1.5		±1.0	±2.0		±1.0	±2.0	mV
SPAN SHIFT (0 TO 25 °C, 25 TO 50 °C) P2>P1 /2\			±1.0	±2.0		±1.0	±1.5		±0.75	±1.5		±0.75	±1.5		±0.5	±1.5		±0.5	±1.5	%SPAN
REPEATABILITY AND HYSTERESIS			±0.5			±0.2			±0.2			±0.2			±0.2			±0.20		%SPAN
OVERPRESSURE (P2>P1; P1>P2)				20			20			45			60			200			500	PSI
ALL PRESSURE RANGES		MIN	NOM	MAX	UNITS															
EXCITATION VOLTAGE			10	16	VDC															
INPUT RESISTANCE		5.5K	7.5K	11.5K	OHMS															
OUTPUT RESISTANCE		1.5K	2.5K	3.0K	OHMS															
RESPONSE TIME				1.0	ms															
TEMPERATURE RANGES																				
STORAGE		-55 °C TO +100 °C (-67°F TO +212°F)																		
OPERATE		-40 °C TO +85 °C (-40°F TO +185°F)																		
COMPENSATED		0 TO +50 °C (+32 °F TO +122 °F)																		

- NOTES
1 SPAN IS THE ALGEBRAIC DIFFERENCE BETWEEN OUTPUT AT MAXIMUM RATED OPERATING PRESSURE AND OUTPUT AT 0 PSI
2 TEMPERATURE ERROR IS CALCULATED WITH RESPECT TO 25 °C
3 - INPUT MEDIA LIMITED ONLY TO THOSE MATERIALS THAT WILL NOT ATTACK SILICON, THE HOUSING MATERIAL OR SEAL MATERIAL
4 - TERMINALS ARE PLATED FOR SOLDERING (LIMIT SOLDERING TO 315 °C FOR 10 SECONDS MAXIMUM)
5 PIN 1 IS IDENTIFIED BY NOTCH IN LEAD
6 - SENSOR IS OPERATIONAL OVER VACUUM PRESSURE RANGE
7 - RATIONOMETRIC TO SUPPLY VOLTAGE
8 CATALOG LISTING AND DATE CODE HERE. ALTERNATE FORMAT OF CATALOG LISTING BRAND IS THE ENTIRE CATALOG LISTING

CIRCUIT DIAGRAM



THIRD ANGLE PROJECTION	
SCALE	3 : 1
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) +.030
TWO PLACE	(.00) +.015
THREE PLACE	(.000) +.005
ANGLES	+
WEIGHT	2 OZ

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.	
FED. MFG. CODE 91929	CATALOG LISTING
MICRO SWITCH a Honeywell Division	BRIDGE PRESSURE SENSOR 26PC SERIES CHART 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[26PCCFJ6D](#) [26PCFNH6D](#) [26PCGNH6D](#) [26PCFFT6D](#)