

MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

SWITCH-BASIC

CATALOG LISTING

V7-2S17E9-420

CW-B8704

CATALOG LISTING
V7-2S17E9-420
PAGE 1 OF 1

M

ISSUE
3

REVISIONS
A REL PR21459
DCS
19 DEC 94
B CO-
93311
TSM
26 OCT 98

REPLACES

RELEASE NO. PR-21459

CHECK

CHECK

19 DEC 94


DCS

CHECK

2 AUG 94

FORMTEK

DRAWN




NOTES
1 - IN INSPECTION, DO NOT BURN OUT - GOLD CONTACTS
2 - IN INSPECTION, DO NOT EXCEED 10 VDC, .1A RESISTIVE LOAD

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 77 GRAMS MAX	CONTACT ARRANGEMENT	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE — — — 6 GRAMS MIN	S P D T			
DIFFERENTIAL TRAVEL — — — .015 MAX	L142 0.1A 125 VAC	ONE PLACE (.0)	±.030	
OVERTRAVEL — — — .038 MIN		TWO PLACE (.00)	±.015	
RELEASE TRAVEL — — — .009 MIN		THREE PLACE (.000)	±.005	
		ANGLES	±	
		WEIGHT		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-2S17E9-420](#)