

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH — BASIC

CATALOG LISTING

V7-4S37D8

CW-B8608

CATALOG LISTING
V7-4S37D8
PAGE 1 OF 1

M

ISSUE
4

REPLACES

RELEASE NO PR-18858

CHECK



CHECK

CHECK

CHECK

CHECK

DCS




NOTES

- 1 — IN INSPECTION, DO NOT BURN OUT — GOLD CONTACTS
- 2 — IN INSPECTION, DO NOT EXCEED 10 VDC, .1A RESISTIVE LOAD

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 25 GRAMS MAX	CONTACT ARRANGEMENT S P N C	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
DIFFERENTIAL TRAVEL — — — .002—.010	L142 0.1A 125 VAC	ONE PLACE (.0)	±.030
OVERTRAVEL — — — — — .050 MIN		TWO PLACE (.00)	±.015
FREE POSITION — — — — — .625 MAX		THREE PLACE (.000)	±.005
RELEASE TRAVEL — — — — — .010 MIN		ANGLES	±
		WEIGHT	



FORMTEK

DRAWN

DCS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-4S37D8](#)