

BA-3ST
 PAGE 1 OF 1

M

DRAWING
 NUMBER

ISSUE
 11

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO	53551
S	L	15 SEPT 83
B	CO	0063005
J	A	P
5	APR	88
C	CO	59351-D
J	WB	18 JUL 91
D	205503	
G	JW	1 MAY 02

CHECK

CHECK

CHECK

CHECK

CHECK



CHECK

CHECK

CHECK

CHECK

CHECK




NOTES

- 1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX. DIA ON 1.000 $\pm$.002 CENTERS
- 2 - SUITABLE ONLY FOR APPLICATIONS IMPARTING A RAPID STROKE TO THE SWITCH PLUNGER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL																				
OPERATING FORCE — — — — 26- 38 OZ	CONTACT ARRANGEMENT SEE CIRCUIT DIAGRAM	DO NOT SCALE PRINT																				
RELEASE FORCE — — — — — 10 OZ MIN	30 VOLTS D C RATING (SEA LEVEL TO 50,000 FT) INDUCTIVE — — — — — 25 AMP RESISTIVE — — — — — 30 AMP MAXIMUM INRUSH — — — — — 75 AMP BASED ON LIFE OF 25,000 OPERATIONS	TOLERANCES APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±																				
DIFFERENTIAL TRAVEL — — — .007 — .015	25A 125, <u>250</u> , OR 480 VAC L58	<table><tr><th>DIM. mm</th><th>TOL. mm/in</th><th>DIM. in</th><th>TOL. mm/in</th></tr><tr><td>NO PLACES</td><td>X</td><td>1/.04</td><td></td></tr><tr><td>ONE PLACE</td><td>X,X</td><td>0.4/.016</td><td>X,X 0.8/.03</td></tr><tr><td>TWO PLACES</td><td>X,XX</td><td>0.15/.006</td><td>X,XX 0.38/.016</td></tr><tr><td>THREE PLACES</td><td>X,XXX</td><td></td><td>X,XXX 0.13/.006</td></tr></table>	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in	NO PLACES	X	1/.04		ONE PLACE	X,X	0.4/.016	X,X 0.8/.03	TWO PLACES	X,XX	0.15/.006	X,XX 0.38/.016	THREE PLACES	X,XXX		X,XXX 0.13/.006
DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in																			
NO PLACES	X	1/.04																				
ONE PLACE	X,X	0.4/.016	X,X 0.8/.03																			
TWO PLACES	X,XX	0.15/.006	X,XX 0.38/.016																			
THREE PLACES	X,XXX		X,XXX 0.13/.006																			
OVERTRAVEL — — — — — .010 MIN	3/4 HP 125 VAC, 1 1/2 HP <u>250</u> VAC 1A 125 VDC, 0.5A 250 VDC	DESIGN UNITS ☐ SI METRIC ☐ US CUSTOMARY ☒																				
		WEIGHT .067 LB																				

RASTER

FO-52848-A

DRAWN

SL B15 SEPT 83

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BA-3ST](#)