

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

BZ-2RW84449-A2

APY0290

BZ-2RW84449-A2
PAGE 1 OF 1

M

DRAWING
NUMBER

8

ISSUE

RELEASE NO. PR-12811 REPLACES X79023-BZ

REVISIONS

CHECK

08DEC05

RJ

CHECK

17 FEB 84

CHECK

CEC

CHECK


16 FEB 84

CHECK

TSK

REVISIONS

A	C080986
JALA	26 JUN 95
B	C093346
DLT	17 SEP 98
C	0017579
KRB	08DEC05




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS
- 2 PLUNGERS SHOULD NOT BE INTERCHANGED AMONG SWITCHES
- 3 - LEVER AND SHAFT FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - - 9-13 OZ

RELEASE FORCE - - - - - 4 OZ MIN

DIFFERENTIAL TRAVEL - - .0004 - .0020

DO NOT OVERTRAVEL MORE THAN - - .020

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

-L96- 15 A - 125, 250, OR 480 VAC
1/2 A - 125 VDC; 1/4 A - 250 VDC
1/8 HP - 125 VAC; 1/4 HP - 250 VAC



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/104	X X
ONE PLACE	X, X	0.4/018	X X X
TWO PLACES	X, X X	0.18/018	X X X X
THREE PLACES	X, X X X	0.11/018	X X X X X

SI METRIC

US CUSTOMARY

DESIGN UNITS ☐

☒

WEIGHT .070 LB

FORMTEK

DRAWN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RW84449-A2](#)