


# HFX6015-XXX

## FOR INDUSTRIAL BUS SYSTEMS

### FEATURES

- Super bright LED for optical fiber communication
- High accuracy by use of special plastic package with centered LED die
- High output at suitable peak wavelength (typ.) for plastic fiber
- High frequency cut-off, most suited for high speed data transmissions ( $f_c = \text{typ. } 7 \text{ MHz}$ )
- HFX6015-200: Metal barrel for high mechanical stability
- HFX6015-200: Separate grounding of barrel for optimum EMI/RFI shielding



opho\_234.TIF

### OUTLINE DIMENSIONS in inches (mm)

#### HFX6015-548 HFX6015-210




Fig. 1

#### HFX6015-200




Fig. 2

ODIM\_232.TIF

OGRA-166.TIF

4551830 0021824 151

# Honeywell

Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

# HFX6015-XXX

## FOR INDUSTRIAL BUS SYSTEMS

### ELECTRO-OPTICAL CHARACTERISTICS

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST
Peak Wavelength	$\lambda_p$		660		nm	$I_F = 30 \text{ mA}^{(1)}$
Spectral Line Half Width	$\Delta\lambda$		30		nm	$I_F = 30 \text{ mA}^{(1)}$
Forward Voltage	$V_F$		2.5		V	$I_F = 30 \text{ mA}^{(1)}$
Reverse Current	$I_R$		4		$\mu\text{A}$	$V_R = 4 \text{ V}$
Capacitance	$C_o$		50		pF	
Response Time	$t_r, t_f$		50		ns	$I_F = 30 \text{ mA}^{(1)}$

Note

1. Derate Linearly from 25°C: 0.93 mA/°C

### HFX6015-200 (FIG.2) SERCOS

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST
Coupled Power	$P_c$	300			$\mu\text{W}$	$I_F = 30 \text{ mA}^{(1)}$ 1 mm fibre

### HFX6015-210 (FIG.1) GENERAL PURPOSE BUS APPLICATIONS

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST
Coupled Power	$P_c$	300			$\mu\text{W}$	$I_F = 30 \text{ mA}^{(1)}$ 1 mm fibre

### HFX6015-4XX PROFIBUS

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST
Coupled Power	$P_c$	-5.5			dBm	1 mm fibre

### HFX6015-4XX PROFIBUS

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	TEST
Coupled Power	$P_c$	400		1100	$\mu\text{W}$	$I_F = 4 \text{ mA}$

### ABSOLUTE MAXIMUM RATINGS

(25°C Free-Air Temperature unless otherwise noted)

Forward current	70 mA
Peak forward current	300 mA
Reverse voltage	+4 V
Power dissipation	140 mW
Operating temperature	-30 to +85°C
Storage temperature	260°C, 5 sec (3,0 mm from body)


4551830 0021825 098

**Honeywell**


Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

# HFX6015-XXX


## FOR INDUSTRIAL BUS SYSTEMS




OGRA\_152.TIF




OGRA\_153.TIF




OGRA\_154.TIF



OGRA\_155.TIF



OGRA\_156.TIF



OGRA\_157.TIF

4551830 0021826 T24

**Honeywell**

Honeywell reserves the right to make changes in order to improve design and supply the best products possible.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[HFX6015-200](#) [HFX6015-210](#)