

590-33AA34-503

([Home](#) : [Products](#) : [Sensors](#) : [Temperature Sensors](#) : [Packaged Temperature Probes](#) : 500)



500 Series surface temperature probe, NTC, 50,000 Ohm, $\pm 0,2\text{ }^{\circ}\text{C}$ [0.36 $^{\circ}\text{F}$] tolerance, 0 $^{\circ}\text{C}$ to 70 $^{\circ}\text{C}$ [32 $^{\circ}\text{F}$ to 158 $^{\circ}\text{F}$] accuracy, aluminum, threaded body (8-32 UNC-2A), flying leads (two), 24 gauge Teflon insulation, 64 mm [2.5 in]

Actual product
appearance may vary.

Product Specifications

Thermistor Type	NTC
Temperature Sensing Type	Surface
Resistance	50,000 Ohm
Tolerance	$\pm 0,2\text{ }^{\circ}\text{C}$ [0.36 $^{\circ}\text{F}$]
Accuracy	0 $^{\circ}\text{C}$ to 70 $^{\circ}\text{C}$ [32 $^{\circ}\text{F}$ to 158 $^{\circ}\text{F}$]
BETA (25/85)	4261
R-T Curve	1
Operating Temperature	-60 $^{\circ}\text{C}$ to 125 $^{\circ}\text{C}$ [-76 $^{\circ}\text{F}$ to 257 $^{\circ}\text{F}$]
Housing Material	Aluminum
Mounting Method/Mechanical Interface	Threaded body (8-32 UNC-2A)
Electrical Interface/Connector Type	Flying leads (two)
Lead Material	28 Gauge Teflon insulation
Lead Length	64 mm [2.5 in]
Time Constant on Metal Surface	3.0 s
Dissipation Constant on Metal Surface	6 mW/ $^{\circ}\text{C}$
Availability	Global
Series Name	500

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[590-33AA34-503](#)