

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH – BASIC

CATALOG LISTING

V3-119

CK-B1900

CATALOG LISTING

V3-119

PAGE 1 OF 1

REPLACES

RELEASE NO.

ISSUE

13

CHECK

REVISIONS

A	OBS	C082209
	CSL	11 NOV 96
B	RE-INST	PR22527
	DCS	18 DEC 96

CHECK



CHECK

18 DEC 96

DCS

DDM/CAD

DRAWN




NOTE
1 – TERMINALS ARE PLATED FOR SOLDERING

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — — 8 OZ MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — — 2 OZ MIN	L156 11A 1/3HP 125, 250 OR 277 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L"	ONE PLACE (.0)	±.030
DIFFERENTIAL TRAVEL — — .006-.016		TWO PLACE (.00)	±.015
OVERTRAVEL — — — — .040 MIN		THREE PLACE (.000)	±.005
FREE POSITION — — — — .625 MAX		ANGLES	±
RELEASE TRAVEL — — — — .007 MIN			WEIGHT .016 LB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3-119](#)