Installation Instructions for the SL353 Series Micropower Omnipolar Digital Sensor ICs

Honeywell

50061206 Rev. B

GENERAL INFORMATION

CAUTION

ELECTROSTATIC DISCHARGE DAMAGE

This component is sensitive to electrostatic discharge (ESD). Take normal ESD precautions in handling this product to prevent ESDinduced damage and/or degradation.

Failure to comply with these instructions may result in product damage.



SOLDERING/ASSEMBLY

CAUTION PRODUCT DAMAGE

- Ensure leads are adequately supported during any forming/ shearing operation so that they are not stressed inside the plastic case.
- Limit exposure to high temperatures.
- Do not wave solder.

Failure to comply with these instructions may result in product damage.

Use an infrared reflow process with temperatures of 245 $^{\circ}\text{C}$ [473 $^{\circ}\text{F}$] peak for 10 s max.

Table 1. Absolute Maximum Ratings

Characteristic	Condition	Min.	Тур.	Max.	Unit
Supply voltage	_	-0.5	_	6	V
Operating temperature	ambient	-40 [-40]	_	150 [302]	°C [°F]
Soldering temperature	applied for <10 s	_	_	265 [509]	°C [°F]
Load current	—	_	_	5	mA

NOTICE

Absolute maximum ratings are the extreme limits that the device will withstand without damage to the device. However, the electrical and mechanical characteristics are not guaranteed as the maximum limits (above recommended operating conditions) are approached, nor will the device necessary operate at absolute maximum ratings.

Figure 1. Block/Electrical Diagram



Table 2. Magnetic Characteristics for SL353 Series (2.2 V \leq Vs \leq 5.5 V, -40 °C [-40 °F] \leq Ta \leq 85 °C [185 °F])

-					
Characteristic	Condition		Тур.	Max.	Unit
Operate point: positive negative	Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F	20 -110	60 -60	110 -20	Gauss
Release point: positive negative	Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F	5 -95	45 -45	95 -5	Gauss
Hysteresis	Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F]	3	15	60	Gauss

NOTICE

The magnetic field strength (Gauss) required to cause the switch to change state (operate and release) will be as specified in the magnetic characteristics. To test the switch against the specified magnetic characteristics, the switch must be placed in a uniform magnetic field.

SL353 Series Micropower Omnipolar Digital Hall-Effect Sensor ICs

Rev. B 50061206

Table 3. Electrical and Environmental Characteristics for SL353 Series

(At 2.2 V ≤ Vs ≤ 5.5 V, -40 °C [-40 °C] ≤ Ta ≤ 85 °C [185 °F] and Vs = 2.8 V, Ta = 25 °C [77 °F] unless otherwise specified.)

•					
Characteristic	Condition	Min.	Тур.	Max.	Unit
Supply voltage (Vs)	Ta = -40 °C to 85 °C [-40 °F to 185 °F]	2.2	2.8	5.5	V
Active mode current	Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F]		2.5 2.5	4 9	mA
Sleep mode current	Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F]		1.5 1.5	2.5 8	μA
Average current: SL353HT SL353HT SL353LT SL353LT SL353LT	Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F] Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F]	 	0. 33 0.33 1.8 1.8	0.64 2.3 3 9	mA mA μA μA
Active mode time	Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F]	3 3	6 6	9 30	μs
Period: SL353HT SL353HT SL353LT SL353LT	Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F] Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F]	30 20 30 20	45 45 45 45	80 150 80 150	μs μs ms ms
Duty cycle: SL353HT SL353HT SL353LT SL353LT SL353LT	Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F] Vs = 2.8 V, Ta = 25 °C [77 °F] Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F]	10 5 0.01 0.005	13 13 0.013 0.013	16 25 0.016 0.025	%
Vout: high high low low	Vs = 2.8 V, Ta = 25 °C [77 °F], load current = 100 μA Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F], load current = 100 μA Vs = 2.8 V, Ta = 25 °C [77 °F], load current = 100 μA Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F], load current = 100 μA	Vs - 0.15 Vs - 0.25 —	Vs - 0.11 Vs - 0.11 0.11 0.11	 0.15 0.25	V
Operating temperature	Vs = 2.2 V to 5.5 V, Ta = -40 °C to 85 °C [-40 °F to 185 °F]	-40 [-40]	-	85 [185]	°C [°F]
Storage temperature	_	-40 [-40]	_	150 [302]	°C [°F]

NOTICE

- These Hall-effect sensors ICs may have an initial output in either the on or off state if powered up with an applied magnetic field in the differential zone (applied magnetic field > Brp and < Bop). Honeywell recommends that the application circuit designer allow 10 µs after apply voltage has reached its rated value for the output voltage to stabilize.
- The sensor will turn LOW when the magnetic field is present and switch to HIGH when the field is removed. The sensor will latch and hold the state during the sleep "mode".

SL353 Series Micropower Omnipolar Digital Hall-Effect Sensor ICs

Rev. B 50061206



SL353 Series Micropower Omnipolar Digital Hall-Effect Sensor ICs

Rev. B 50061206

Figure 3. Mounting and Tape/Reel Dimensions (For reference only. mm/[in].)



SL353 Series Macropower Omnipolar Digital Hall-Effect Sensor ICs

WARNING PERSONAL INJURY

DO NOT USE these products as safety or emergency stop devices or in any other application where failure of the product could result in personal injury.

Failure to comply with these instructions could result in death or serious injury.

WARRANTY/REMEDY

Honeywell warrants goods of its manufacture as being free of defective materials and faulty workmanship. Honeywell's standard product warranty applies unless agreed to otherwise by Honeywell in writing; please refer to your order acknowledgement or consult your local sales office for specific warranty details. If warranted goods are returned to Honeywell during the period of coverage, Honeywell will repair or replace, at its option, without charge those items it finds defective. **The foregoing is buyer's sole remedy and is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose. In no event shall Honeywell be liable for consequential, special, or indirect damages.**

While we provide application assistance personally, through our literature and the Honeywell web site, it is up to the customer to determine the suitability of the product in the application.

Specifications may change without notice. The information we supply is believed to be accurate and reliable as of this printing. However, we assume no responsibility for its use.

Honeywell serves its customers through a worldwide network of sales offices, representatives and distributors. For application assistance, current specifications, pricing or name of the nearest Authorized Distributor, contact your local sales office or:

E-mail: info.sc@honeywell.com Internet: sensing.honeywell.com Phone and Fax: USA/Canada +1-800-537-6945 International +1-815-235-6847; +1-815-235-6545 Fax

Sensing and Control Honeywell 1985 Douglas Drive North Golden Valley, MN 55422 honeywell.com

Honeywell

50061206-B-EN IL50 April 2015 © 2015 Honeywell International Inc. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell: SL353HT SL353LT