



PIN 1 =  $V_s$   
 PIN 2 =  $V_{+0}$   
 PIN 3 =  $V_g$   
 PIN 4 =  $V_{-0}$



FORCE SENSOR				
(at 10.00±.01 VDC Excitation, 25° C)				
PARAMETER	MIN	NOM	MAX	UNITS
NULL OFFSET	-30	0	+30	mV
SPAN (at 1500 gms, dead weight)	290	360	430	mV
	MIN	TYP	MAX	UNITS
LINEARITY		±0.5		% SPAN
INPUT RESISTANCE		5.0K		OHMS
OUTPUT RESISTANCE		5.0K		OHMS
EXCITATION VOLTAGE	RATIOMETRIC	10	12	VDC
OPERATING FORCE	0		1500	GRAMS
OVER FORCE			5500	GRAMS
OPERATING TEMPERATURE (-40° to +90°C)				
STORAGE TEMPERATURE (-55° to +105°C)				
VIBRATION 0 to 2KHz, 20g SINE				
SHOCK TESTED TO 150g				

NOTES

- 1 - DEVICE IS ELECTRICALLY RATIOMETRIC
- 2 - DEVICE CAN OPERATE WITH CURRENT EXCITATION
- 3 - ALL FORCE RELATED SPECIFICATIONS ESTABLISHED BY USING DEAD WEIGHT OR COMPLIANT FORCE
- 4 - TYPICAL FULL SCALE DEFLECTION .03 MM

OBSOLETE

THIRD ANGLE PROJECTION		
SCALE 5 : 1		
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	±.030
TWO PLACES	(.00)	±.015
THREE PLACES	(.000)	±.005
ANGLES		±
WEIGHT		

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

**MICRO SWITCH**  
 a Honeywell Division

**FORCE SENSOR**

**FSG15N1A1**

CATALOG LISTING

P.T.C./CAD 3D	DRAWN	KED	10 JAN 00	CHECK	SAV	CHECK	RS	CHECK	10 JAN 00	CHECK	RS	CHECK	07 NOV 12	SK	09 MAY 07	A 0030657	REVISIONS	3	DRAWING NUMBER	M	FSG15N1A1	ISSUE	3	DRAWING NUMBER	M	FSG15N1A1	PAGE 1 OF 1	RELEASE NO. PR-24338	REPLACES

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[FSG15N1A](#)