




































HONEYWELL
PART NUMBER



102TL2887 SERIES CHART 2

REV	DOCUMENT	CHANGED BY	CHECK
5	0008691	KSR 25OCT04	AK











CATALOG LISTING 	AVAILABLE LOCKING COMBINATIONS FOR CONFIGURATION SEE LETTERED DETAILS	CIRCUIT MADE  WITH TOGGLE LEVER IN			ELECTRICAL RATING
		KEYWAY SIDE (1-2, 4-5)	CENTER (1-2, 4-5)	OPPOSITE KEYWAY (2-3, 5-6)	
102TL2887-1	A,B,D,E,F,G,H,J,K,L,M,N,P	ON	OFF	ON	.1A 28 VDC, 115 VAC
102TL2887-2	D,F,G	OFF	NONE	ON	
102TL2887-3	D*,F,G	ON	NONE	ON	
102TL2887-21	E,F,K,M	NONE	OFF	ON	
102TL2887-31	E,F,K,M	NONE	ON	ON	
102TL2887-4	F	MOM OFF	NONE	ON	
102TL2887-5	E,F,K,L,M,N	MOM ON	OFF	ON	
102TL2887-6	F	MOM ON	NONE	OFF	
102TL2887-7	E,L,N	MOM ON	OFF	MOM ON	
102TL2887-8	F	MOM ON	NONE	ON	
102TL2887-51	E	NONE	ON	MOM ON	
102TL2887-61	E	MOM ON	OFF	NONE	


  LOCKED IN THREE POSITIONS	  LOCKED IN CENTER AND EXTREME POS. (KEYWAY SIDE)	  LOCKED OUT OF CENTER POSITION	  LOCKED IN CENTER POSITION	  LOCKED IN EXTREME POS. (OPP. KEYWAY)	  LOCKED IN EXTREME POS. (KEYWAY SIDE)										
  LOCKED OUT OF CENTER AND EXTREME POS. (KEYWAY SIDE)	  LOCKED OUT OF CENTER AND EXTREME POS. (OPP. KEYWAY)	  LOCKED IN CENTER AND EXTREME POS. (OPP. KEYWAY)	  LOCKED OUT OF EXTREME POS. (KEYWAY SIDE)	  LOCKED OUT OF AND INTO EXTREME POS. (OPP. KEYWAY)	  LOCKED OUT OF EXTREME POS. (OPP. KEYWAY)										
  LOCKED OUT OF AND INTO EXTREME POS. (KEYWAY SIDE)	 LOCKWASHER 					 LOCKING RING 					 2X HEX NUT 				

MOVED  

* FAA-PMA APPROVED  

NOTES

- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160° F CONTINUOUSLY AT FULL RATED LOAD
- 2 - CIRCUIT DESIGNATION, AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
-  FURNISHED UNASSEMBLED
-  KEYWAY SHOWN ON LEFT SIDE
-  SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE OF TOGGLE LOCKING, SEE CHART FOR AVAILABLE LOCKING COMBINATIONS
-  APPLIES ONLY TO "ON" AND "MOM ON" POSITIONS
-  THE SEALING GROMMET SHALL SEAL ON A SMOOTH WIRE INSULATION OF .040 TO .083 DIAMETERS (16-20 GAGE)
- 8 - UNUSED TERMINAL HOLES MAY BE SEALED WITH PLUGS M83723/28-20
-  FROM BOTTOM OF KEYWAY TO MAJOR Ø OF 15/32 THREAD
- 10 - GOLD PLATED CONTACTS
-  FAA-PMA TO BE MARKED ON THESE SWITCHES
-  FOR MANUFACTURING DETAIL SEE THE CORRESPONDING ASSEMBLY DRAWING FOR EACH LISTING FOR FAA-PMA

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± 0.040 ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± 0.0005 ANGLES ± 2 THIRD ANGLE PROJECTION 	DRAWN	KSR	25OCT04	Honeywell				
	CHECK	AK	25OCT04					
	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - TOGGLE				
	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE C	TYPE I	DRAWING NAME 102TL2887 SERIES CHART 2		REV 5
	RASTER			SCALE 1 : 1	WEIGHT .137 LBS. MAX		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[102TL2887-7L](#)