

## CSNF661

( [Home](#) : [Products](#) : [Sensors](#) : [Current Sensors](#) : [Closed Loop](#) : [CSN](#) )



CSN Series closed loop current sensor, measures ac, dc or impulse current, 100 A nominal,  $\pm 150$  amp range, offset pin, 1000 turn

Actual product appearance may vary.

### Product Specifications

Product Type	Closed Loop Linear
Sensed Current Type	ac or dc
Sensed Current Range	$\pm 150$ A
Package Type	Thru Hole PCB Mount
Output Type	Current
Continuous Current	$\pm 150$ A
Operate Current	100 A RMS @ 25 °C
Supply Current	$\pm 10$ mA + Output
Supply Voltage	$\pm 12.0$ Vdc to $\pm 15.0$ Vdc
Offset Current	$< \pm 0.2$ mA
Offset Current Drift	$< \pm 0.5$ mA
Coil Resistance	30 Ohm
Response Time	$< 0.5$ $\mu$ s
Coil Turns	1000
Output Nominal	100 mA
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Storage Temperature	-40 °C to 90 °C [-40 °F to 194 °F]
Measuring Resistance	30 Ohm min., 80 Ohm max.
Housing Material	Glass-filled PBT (UL94-V0)
Mounting	PCB on 3 Pins
Pinout Style	Offset
Accuracy	$\pm 0.5$ %
Availability	Global
Comment	Offset pin version of CSNF161.
UNSPSC Code	41111928
UNSPSC Commodity	41111928 Current Sensors
Series Name	CSN

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[CSNF661](#)